


LOC	DIST	REVISIONS				
CE	16	P	LTR	DESCRIPTION	DATE	DWN
			B	REVISED PER ECR-08-003988	05MAR08	JWD
						APVD
						JD

- 1

MAXIMUM INSERTION LOSS IS 0.5dB (SC) AND 0.2 dB (LC) PLUS CABLE ATTENUATION OF 0.7 dB/km AT 1310nm. (SEE TABLE)
2.

MINIMUM RETURN LOSS: 55dB
3.

PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702.



0.54	0.24	30.00±0.30	[1181.1±12.0]	3-6374611-0
0.53	0.23	25.00±0.30	[984.3±12.0]	2-6374611-5
0.51	0.21	20.00±0.30	[787.0±12.0]	2-6374611-0
0.51	0.21	15.00±0.15	[591.0±6.0]	1-6374611-5
0.51	0.21	10.00±0.15	[393.7±6.0]	1-6374611-0
0.50	0.20	8.00±0.15	[315.0±6.0]	6374611-7
0.50	0.20	2.60±0.05	[102.3±2.0]	6374611-6
0.50	0.20	5.00±0.08	[196.9±3.0]	6374611-5
0.50	0.20	4.00±0.08	[157.5±3.0]	6374611-4
0.50	0.20	3.00±0.05	[118.1±2.0]	6374611-3
0.50	0.20	2.00±0.05	[78.7±2.0]	6374611-2
0.50	0.20	1.00±0.05	[39.4±2.0]	6374611-1
MAX IL (dB) SC		MAX IL (dB) LC	L METERS [INCHES]	PART NUMBER

1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
KATHY HE
28SEP05

CHK
RICHARD ZHAO
28SEP05

APVD
J. DUNCAN
28SEP05

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Tyco Electronics

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME
CABLE ASSY, FIBER OPTIC, 2.0mm SINGLEMODE LDS, AMP SC TO LC

SIZE
A2

CAGE CODE
00779

DRAWING NO
6374611

RESTRICTED TO
B

SCALE
NTS

SHEET
1 of 1

REV
B