


Pin Header SMD Shrouded 1,25 mm

Series

427




Rated current	1,0 A
Rated voltage	100 V _{RMS} / V _{DC}
Withstand voltage	300 V _{RMS} for one minute
Material contact	Copper alloy
Material insulator	High temp. thermoplast UL94V-0
Operating temperature	-40°C to +105°C
Max. processing temper.	260°C for 10 seconds

pitch	1,25
termination	
max. pincount	015


All dimensions in mm.

Product group
3

Variation





1



2

PCB Layout



Plating:
T = Sn

Packaging:
S = Standard
R = Reel

Variation (1,2)

No. of contacts

Plating contact

Packaging (S,R)



www.mpe-connector.de

Order code:

427-2-222-0-T-K20

Mating series
see page

425
6-3