

Sealed Vehicle Rockers

Sealed vehicle rockers are a unique automotive-styled switch line with IP67 sealing and innovative lighting technology. This line offers a wide range of circuits, actuator styles and accessories for instrument panel design in construction, off-road, and marine vehicles.



Stock No.	Mfr.'s Type	Contact Form	Action (Momentary)	Illumination	EACH		
					1-24	25-49	50+
757-5000	S2003SN00	DPDT	On-None-On	—	12.81	11.65	10.68
757-5001	S2541SN20	DPDT	On-None-On	14 V green LED top	22.98	20.89	19.16
757-5002	S2548SN22	DPDT	On-None-On	14 V green LEDs top and bottom	21.07	19.16	17.57
757-5003	S2004SN00	DPDT	On-Off-On	—	13.33	12.11	11.11
757-5005	S2568SN22	DPDT	On-Off-On	14 V green LEDs top and bottom	22.00	20.00	18.33
757-5049	S2005SN00	DPDT	(On)-Off-(On)	—	15.26	13.87	12.71
757-5050	S2588SN22	DPDT	(On)-Off-(On)	14 V green LEDs top and bottom	23.95	21.77	19.96

Rocker Actuators



Stock No.	Mfr.'s Type	Description	EACH		
			1-24	25-49	50+
757-5051	100000000	Plain Black Rocker	1.67	1.52	1.40
757-5052	2B0000000	Black Rocker, Green Snap-In-Lens, Top	2.25	2.05	1.88
757-5053	4B000B000	Black Rocker, Green Snap-In-Lens, Top and Bottom	1.25	1.14	1.05
757-5054	500000000	Plain Black Paddle Rocker	2.27	2.07	1.89

Accessories

757-5055	25-13936	Connector	.84	.76	.70
757-5056	17-22145	Panel plug	.97	.88	.82
757-5057	17-22146	Gang mount system	1.09	.98	.90

AC-DC Rated Toggle Switches

Quick-make, quick-break contact with wiping action. Arc-resistant. 5/32" diameter bushing; mounting hardware included. UL and CSA listed. All have 11/32" bushing length, except * have 15/32". Weight: 2 ozs.



Single Pole 2-Position Switches

Stock No.	Mfr.'s Type	Action	Amps @		Terminals	EACH	
			125 V	250 V		1-24	25-49
757-6302	8280K115	On-Off	—	3	Solder	6.05	5.01
757-6555	8295K107	On-Off	—	3	Screw	6.42	5.49
757-7040	8381K107	On-Off	6	3	Solder	5.06	4.34
757-7097	8396K108*	On-Off	6	3	Screw	9.12	7.81
757-7096	8396K107	On-Off	6	3	Screw	7.73	6.41


*15/32" bushing.

Double Pole 2-Position Switches

Stock No.	Mfr.'s Type	Action	Amps @		Terminals	EACH	
			125 V AC-DC	250 V DC		1-24	25+
757-6840	8370K107*	On-Off	6	3	Solder	8.09	6.93
757-6895	8372K107*	On-Off	6	3	Screw	10.59	9.25
757-6910	8373K107*	On-On	7	3	Solder	10.15	8.57

*15/32" bushing.

AC Rated Toggle Switches



Single Pole


Stock No.	Mfr.'s Type	Action	Amps @		HP @ 250 VAC	Terminals	EACH	
			125 V	250 V			1-24	25-49
757-4885	7580K4	On-Off	6	3	—	Screw	3.99	3.43
757-4888	7580K7*	On-Off	6	3	—	Solder	3.74	3.15
757-4887	7580K6†	On-Off	6	3	—	Solder	3.61	3.09
757-4001	7500K14	On-Off	15	10	3/4	Screw	3.92	3.25
757-4021	7501K13	On-Off	15	10	3/4	Solder	3.27	2.78
757-4022	7501K15	On-Off	15	10	3/4	0.250 Spade	3.26	2.73
757-4201	7504K4	On-On	15	10	3/4	Screw	5.13	4.27
757-4070	7502K13	On-Off-On	15	10	3/4	Screw	5.13	4.40
757-4270	7509K5	On-Off-On	—	10	1/2	Screw	7.04	6.00

Double Pole

757-4940	7590K4	On-Off	6	3	—	Screw	6.04	5.16
757-4942	7590K6	On-Off	6	3	—	Solder	6.19	5.13
757-4500	7560K5	On-Off	15	10	3/4	Screw	8.47	7.08
757-4560	7561K4	On-Off	15	10	3/4	Solder	6.71	5.61
757-5006	7592K6	On-On	6	3	—	Solder	5.41	4.51
757-4760	7564K6	On-On	15	10	3/4	Screw	7.62	6.51
757-4805	7565K5	On-On	15	10	3/4	Solder	6.22	5.33
757-4807	7565K7	On-On	15	10	3/4	0.250 Spade	6.68	5.72
757-4970	7591K4	On-Off-On	6	3	—	Screw	7.60	6.52
757-4590	7562K4	On-Off-On	15	10	3/4	Screw	9.77	8.13
757-4720	7563K4	On-Off-On	15	10	3/4	Solder	6.68	5.72

*Bushing = 0.344". †Bushing = 0.469".

MIL-S-83731 Lever Seal Switches



Lever Seal Toggle. Tinned screw terminals, except * solder lugs. All are single throw except † which indicates double throw. Weight: 2 ozs.

Single Pole

Stock No.	Mfr.'s Type	Gov't MS No.	Action (Momentary)	EACH		
				1-14	15-24	25+
757-3822	8261K22*	25098-22	On-None-Off	21.78	16.75	16.34
757-8701	8801K22	35058-22	On-None-Off	15.64	13.96	12.78
757-8680	8800K16†	35058-21	On-Off-On	17.68	15.93	14.60
757-8750	8810K15†	35058-23	On-None-On	16.75	15.12	13.82
757-8770	8812K14†	35058-27	(On)-Off-(On)	24.43	21.87	19.91

Double Pole

757-8845	8820K16†	35059-21	On-Off-On	22.91	20.88	18.91
757-8855	8822K20	35059-22	On-None-Off	12.67	11.78	10.94
757-8869	8824K14†	35059-23	On-None-On	24.37	21.96	20.11
757-8904	8834K5†	35059-27	(On)-Off-(On)	30.51	27.48	25.15

*Solder lug terminals. †Double throw.