

HEYCO



Heyco® Double D Hole Plugs

For Mounting Holes with Flats

Multiple Locking Steps for Panel Thickness up to .125" (3,2 mm)




- **Close unwanted Strain Relief mounting holes** or other double faced or Double D holes punched or molded with two opposing flats.
- Convex, matte finish head tapers to a thin edge.
- Quick and easy installation.
- Lock firmly in panels up to .125" (3,2 mm) thick.
- Locking fingers in fractional increments up to the maximum panel thickness.
- Approximate Head Thickness: .062" (1,6 mm). Thickness may vary.

PANEL DIMENSIONS				PART NO.		DESCRIPTION	PART DIMENSIONS			
C		D					A		B	
Mounting Hole Dia. in.	mm.	To Prevent Rotation in.	mm.	Black	White		Head Diameter in.	mm.	Overall Height in.	mm.
.375	9,5	.345	8,8	2617	2618	DP 375*	.468	11,9	.406	10,3
.437	11,1	.390	9,9	2488	2489	DD 437-390	.531	13,5		
.500	12,7	.445	11,3	2491	2492	DD 500-445	.554	14,7		
.562	14,3	.530	13,5	2494	2495	DD 562-530	.656	16,7		
.625	15,9	.550	14,0	2497	2498	DD 625-550	.728	18,5		
.750	19,1	.625	15,9	2503	2504	DD 750-625	.921	23,4		
.875	22,2	.770	19,5	2509	2510	DD 875-770	1.016	25,8	.453	11,5
				2511	—	DD 875-770-9**	.938	23,8		
1.109	28,2	1.000	25,4	2717	2718	DD 1109-1000	1.218	30,9		
2.000	50,8	1.875	47,6	2959	2963	DD 2000-1875	2.170	55,1	.478	12,1

Standard color black. Consult Heyco for other colors.

*On installation, DP 375 Locking Fingers must be aligned with Mounting Hole Flats.

**Smaller than standard Head Diameter, for clearance situations.



MOUNTING HOLE

*Quick
Specs*

**Material
Certifications**

Nylon 6/6



Recognized under the Component Program of Underwriters' Laboratories File E51579



Certified by the Canadian Standards Association File 8919

**Flammability Rating
Temperature Rating**

94V-2

-40°F (-40°C) to 221°F (105°C)