



Save as PDF



9410 LED



1.360 g + 741 LUMENS = BRIGHTEST & LIGHTTEST IN ITS CLASS

At just 1.360 grams and 741 lumens, the new 9410 LED Lantern packs the power without the weight. Four LEDs, powered by the latest generation NiMH batteries illuminate a distance of 416 meters. And it's loaded with innovative technology and features you have come to expect from Peli:

- 120° rotating head
- Burn time: 4.45 hrs. (low)/1.30 hrs. (high)
- Battery status indicator
- 3 mode switch (High, Low, Flashing)
- 22.2 x 9.5 10.2 cm (8.75" x 3.75" x 4.0") L x W x H

Whether you're on a Urban Search and Rescue (USAR) team or the 3rd shift at a refinery, you'll appreciate the compact size and high output of the new 9410 LED Lantern.

Approved to NFPA (National Fire Protection Agency) 1901



Materials

Body	Lens	Shroud	Switch Type
ABS	Polycarbonate	EXL	Push button multi-functional switch - high, low & flashing
Clip	Contact, Spring & Retainer	O-Ring	Night Vision Film
NA	NA	EPDM gasket	NA

Configuration

Cat. #	Description
--------	-------------

9410 LED Accessories

Cat. #	Description

9410 LED ANSI FL1 Specifications

LIGHT SOURCE.	High LED
BATTERIES	4 D Ni-MH (Included)
CHARGE TIME	NiMH Battery Pack 5 hours
VOLTAGE	4.8
LENGTH	22.2 cm (8.75")
WEIGHT W/ BATTERIES	0.14 kg (4.8 oz.)
WEIGHT W/O BATTERIES	

FL1 STANDARD	High	Low
LIGHT OUTPUT 		
RUNTIME (hours/min) 	1h 45m	
BEAM DISTANCE (meters) 	425m	249 m.
PEAK BEAM INTENSITY (candela) 	45260cd	15516cd