



LOC		DIST		REVISIONS				DATE		APPD	
G		86		P	F	ZONE	LTR	DESCRIPTION			
							J	REVISED & REDRAWN PER 0720-0619-95		05JUN95	
										OKS AJK	



1 STAMP AMP 12-10 AL90CU APPROX AS SHOWN



OBsolete

		BODY: COPPER PER ASTM B-152 TIN PL 0.00381[.000150] MIN THK PER MIL-T-10727		51979-4	
6.73±0.13 [.265±.005]		1/4		51979-3	
5.00±0.08 [.197±.003]		#10		51979-2	
4.34±0.08 [.171±.003]		#8		51979-1	
3.68±0.08 [.145±.003]		#6		51979	
'A'		'B'		MATERIAL & FINISH	
				PART NO	
AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX		AMP AMP Incorporated Harrisburg, PA 17105-3608	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		NAME TERMINAL, RING TONGUE, STRANDED/SOLID, COPALUM™, WIRE SIZE: 12-10 AWG	
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		SIZE C 00779	
FOR ORDER ENTRY		1-800-526-5142		DRAWING NO C=51979	
				SCALE 5:1	
				SHEET 1 OF 1	