

Search Results

- Evaluate
 - FAQ's
 - Line Cards
 - PDF-Copper Cabli ..
 - Product Bulletins
 - PDF-TX6A-SD 10Gi ..
 - Technology Briefs
 - PDF-Panduit, Cis ..
 - PDF-Panduit, Cis ..
 - Videos
 - WMV-Ecosystem Su ..
 - WMV-Panduit and ..
- Design a Solution
 - Specification Sheets
 - PDF-TX6A-SD 10Gi ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor
- Install & Maintain
 - Installation Instructions
 - PDF-Mini-Com TX6 ..

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'PUP6ASD04BU-UG'

Your search criteria matched only one product, shown below

PUP6ASD04BU-UG



- Exceeds electrical and alien crosstalk requirements of ANSI/TIA-568-C.2 Category 6A, IEEE 802.3an-2006, and ISO 11801 Class E_A channel standards up to 70 meters (229 feet)
- Meets IEEE 802.3af and IEEE 802.3af for PoE applications
- Patent-pending cable design suppresses alien crosstalk with enhanced internal electrical performance
- Round cable design with reduced cable diameter enables improved cable bundling and optimizes fill capacity
- Ideal for distances up to 70 meters, offering smaller cable diameter compared to Category 6 cable; cable diameter 0.240 in. (6.1mm) nominal
- Installation temperature range: 32°F to 140°F (0°C to 60°C)
- Operating temperature range: -4°F to 167°F (-20°C to 75°C)
- Descending length cable markings enable easy identification of remaining cable which reduces installation time and cable scrap

▪ Part Number	PUP6ASD04BU-UG
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Category 6A, plenum (CMP), 4-pair, UTP copper cable. Copper conductors are 26 AWG with FEP insulation. Conductors are twisted in pairs, separated by an integrated pair divider, surrounded by a patent-pending MaTriX tape and protected by a low smoke flame-retardant PVC jacket. Ideal for installations up to 70 meters. Smallest diameter Category 6A UTP cable on the market at 0.240 in. (6.1mm).
▪ Product Type	Copper Cable
▪ Color	Blue
▪ Cable Color	Blue
▪ Cable Type	UTP
▪ CE Compliant	No
▪ Flammability Rating	CMP
▪ Performance Level	Category 6A/Class EA
▪ Pricing Description	Copper Cable, Cat 6A, 4-Pair, 26 AWG, UTP, CMP, Blue, 1000 Feet/305m
▪ Min. Order UOM	FT
▪ Min. Order Qty.	9000
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.