



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HM	00		H	REV PER ECO-14-004548	26MAR2014	GG	JG



- △1 DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- △2 MATERIAL:
HOUSING - 94V-0 RATED POLYCARBONATE, CLEAR
TERMINAL - .36 [.014] THICK PHOSPHOR BRONZE PLATED WITH .178 μ m[.000007] THICK GOLD IN LOCALIZED PLATE AREA, OVER .762 μ m[.000030] THICK PALLADIUM NICKEL IN LOCALIZED PLATE AREA OVER 2.54 μ m[.000100] THICK NICKEL ON ENTIRE CONTACT.
SHIELD - COPPER ALLOY WITH 1.27 μ m[.000050] MINIMUM SEMI-BRIGHT(SATIN) NICKEL.
LOAD BAR - PBT POLYESTER, BLACK.
3. PLUG WILL ACCEPT A 24 OR 26 AWG STRANDED CONDUCTOR, PROVIDED THE INSULATED CONDUCTOR DIAMETER IS 0.89[.035] TO 0.99[.039] WITH A SHIELDED, PLIABLE, LOOSE CABLE JACKET OF 4.83[.190] TO 5.21[.205] DIAMETER OR A SHIELDED, RIGID, HARD CABLE JACKET OF 4.83[.190] TO 5.08[.200] DIAMETER.
- △4 TERMINATED DIMENSION 6.15 [.242] MAXIMUM.
- △5 500 ASSEMBLIES AND 500 LOAD BARS PER PACKAGE.
- △6 100 ASSEMBLIES AND 100 LOAD BARS PER PACKAGE.
- △8 UL RECOGNIZED: FILE NUMBER E81956.

△6	5-569552-3
△5	5-569552-2
PACKAGED	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. GARRETT 10-12-95		 TE Connectivity			
		CHK C. WHITT 10-31-95					
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME MODULAR PLUG ASSEMBLY, 8 POSITION,SHIELDED,ROUND CABLE, STRANDED WIRE,HIGH PERFORMANCE			
		APVD E. LAURER 11-7-95					
		PRODUCT SPEC 108-1163					
		APPLICATION SPEC 114-6053					
MATERIAL 		FINISH 		SIZE A2	CAGE CODE 00779	DRAWING NO C=569552	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 of 1	REV H	