






PART NAME	NBF SERIES PLASTIC NEMA BOX		PART No.	NBF-32024 & NBF-32124 & NBF-32224 & NBF-32324 & NBF-32424		REVISION DATE	8/12/2010
MATERIAL	FLAMMABILITY RATING	CONTINUOUS OPERATING TEMP.	FINISH: BODY_____ LIGHT GRAY				
ABS	UL94-HB	-40℃ ~ +60℃ / -40℉ ~ 140℉	COVER_____ LIGHT GRAY OR CLEAR				
CLEAR PC	UL94-V0 UV STABILIZED	-40℃ ~ +130℃ / -40℉ ~ 266℉	LATCHES & HINGES_____ PLASTIC				
ABS / PC BLEND	UL94-5VA	-40℃ ~ +85℃ / -40℉ ~ 185℉	WALL MOUNTING BRACKETS__ STAINLESS STEEL & HARDWARE				
PBT / PC BLEND	UL94-5VA + UV (f1)	-40℃ ~ +75℃ / -40℉ ~ 167℉					

COVER



Ø.157in [4.00mm]
FOR M5 x 10mm LG. SELF-TAPPING SCREWS (ABS VERSIONS ONLY)
M5 THREADED INSERTS ON ALL OTHER VERSIONS
USE M5 x 8mm LG. MACHINE SCREWS.



- NOTES:
- 1) UNIT COMES COMPLETE WITH (4) WALL MOUNTING BRACKETS & (4) M5 x 10mm LG. SELF-TAPPING SCREWS. (NOT SHOWN)
 - 2) BOXES DESIGNED TO MEET FOLLOWING STANDARDS: NEMA 1,2,4,4X, AND IEC529-IP65 REQUIREMENTS.

TOLERANCE:
ALL DIMENSIONS HAVE ±0.039in [±1mm]
TOLERANCE UNLESS OTHERWISE SPECIFIED.

PART NO.	MATERIAL		USE
	BODY	COVER	
NBF-32024	ABS	ABS	INDOOR
NBF-32124	ABS / PC	ABS / PC	INDOOR
NBF-32224	ABS / PC	CLEAR PC	INDOOR
NBF-32324	PBT / PC	PBT / PC	OUTDOOR
NBF-32424	PBT / PC	CLEAR PC	OUTDOOR