


Slim Line

Ultra-low-profile compact keyboard with 86 keys

ML technology with Gold Crosspoint contacts

G84-4100



Keyboard with spill-resistant membrane for laboratory and medical environments.



Other approvals available on request.



Microsoft is a registered trademark of Microsoft Corporation.

General

This high-quality, ultra-flat compact keyboard has been designed for all applications where reduced space requirements and low weight are of great importance.

- For banking/financial applications or medical environments and for portable systems
- Also suitable for 19-inch rack applications
- Ideal for use with Slim Line PCs and notebook computers
- Ideal companion for G84-4700

Key benefits

- Uses mechanical keys from our ML series with high-precision key action; small physical dimensions:
- Keycaps arranged in 18 mm grid
- Exceptionally space-efficient
- Lightweight
- LED indicators for Num Lock, Caps Lock, Scroll Lock
- Reliability: MTBF: 170,000 hours
Individual keys have long service life: 20 million key operations

Technical specifications

Power supply:
3.3-5 V/DC $\pm$ 10% SELV

Current input:
typ. 10 mA

Connecting cable:
approx. 1.70 m long

Temperature range:
Storage temperature:
-20 °C to +60 °C
Operating temperature:
0 °C to +50 °C

Housing dimensions:
(L x W x H)
282 x 132 x 27 mm

Weight:
approx. 500 g

ML key modules with
Gold Crosspoint contacts

Actuation characteristics:
Soft contact



External keyboard for pen-based computer.

Order descriptions

G84-4100 PCM..⁽¹⁾

USB interface (Combo, i.e. PS/2 possible using adapter included),

G84-4100 PTM..⁽¹⁾

USB interface (Combo, i.e. PS/2 possible using adapter included),
black

⁽¹⁾ International layouts

BE	=	Belgian
CH	=	Swiss
DE	=	German
DK	=	Danish
ES	=	Spanish
FR	=	French
GB	=	English (UK)
IT	=	Italian
NO	=	Norwegian
PO	=	Portuguese
SF	=	Swedish/Finnish
EU	=	English (US) with €

Other versions available on request.