

FEATURES:








- Half pitch 1.27mm(.050) series
- Centronic female connector I.D.C type for cable
- Panel mount receptacle assemblies bracket with latch block
- Fully EMI/RFI shielded

MATERIALS:

- Housing : Plastic thermoplastic P.B.T UL94V-0 black
- Contacts: Phosphor bronze gold selective plated
- Front Shell: Steel, Nickel plated over copper
- Latch: Steel, Nickel plated over copper

ELECTRICAL:

- Current Rating: 1 Amp
- Insulation Resistance: 500M Ω /Min
- Withstanding Voltage: 500V AC/Min
- Contact Resistance: 35m Ω Max
- Temperature Range: -55°C ~ +105°C

Termination Cover
(1 Places)Wire Holder
(2 Places)

MD5 ID 20 F 0 L 3 7

SERIES

Flat cable IDC termination

NUMBER OF CONTACT:

CONTACT TYPES:

F = female

CONTACT PLATING:

- 0 = selective flash gold
- 1 = selective 15u" gold
- 2 = selective 30u" gold

FIXING DEVICE:

L : Latching + Jackscrews
S : jackscrews only

THREADED HOLES:

3 = M2.6

WIRE HOLDER:

- 6= 0.62mm
- 7= 0.75mm
- 9= 0.9mm

Amphenol Socapex
Usine de DoleECH. ENS.
N SERIE

DOSSIER

DATE DU TIRAGE

DESIGNATION

MINI D SERIES

TOL. GEN.

VOLUME PIECE

SURFACE PIECE

PROTECTION

TRAITEMENT

MATIERE

CLIENT

MODIFICATIONS

EXEC.

DATE

Approb

IND.

N INTERNE

MD5 ID 20 F

COMMUNICATION ET UTILISATION INTERDITES SAUF AUTORISATION