




AC Adapter 12VDC/1000mA

412-112103

DIMENSIONS: mm (in.)



■ Mechanical Specifications:

- Primary voltage: 120VAC 60Hz 30W
- Exciting current, open circuit: 70mA max.
- DC resistance $\pm 15\%$: 51Ω
- Secondary, no load voltage: 17.3VDC
- Loaded voltage: 12VDC @ 1000mA
- DC resistance $\pm 10\%$: 0.80Ω
- Insulation resistance: $100M\Omega$ @ 500VDC
- Dielectric strength: primary-secondary: 1,500VAC for 1 minute
primary-core: 1,500VAC for 1 minute
secondary-core: 500VAC for 1 minute
- Temperature rise: 65°C max. @ rated load
- Cord length: 6ft.

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

412-112103