

GRM0336S1HR10BD01#

" # " indicates a package specification code.

Available

Reflow OK

Complies with RoHS

Ultra-compact

< List of part numbers with package codes >
GRM0336S1HR10BD01D , GRM0336S1HR10BD01J , GRM0336S1HR10BD01C , GRM0336S1HR10BD01B

Shape



L size	0.6 ± 0.03mm
W size	0.3 ± 0.03mm
T size	0.3 ± 0.03mm
External terminal width e	0.1 to 0.2mm
Distance between external terminals g (Min.)	0.2mm
Size code in mm(inch)	0603 (0201)

References

Packaging	Specifications	Minimum quantity
D	Paper tape (φ 180mm)	15000
J	Paper tape (φ 330mm)	50000
B	Packing in bulk	1000

Mass (typ.)	
1 piece	0.33mg
Reel (φ 180mm)	118g

Specifications

Capacitance	0.10pF ± 0.1pF
Rated voltage	50Vdc
Temperature characteristics (complied standard)	S2H(EIA)
Temperature coefficient	-330 ± 60ppm/
Temperature range of temperature characteristics	25 to 85
Operating temperature range	-55 to 125

 Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it ’ s specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.