




(2.00 mm) .0787"

TSH, TMMS SERIES

SHROUDED HEADERS

Mates with:

CLT, SQT, SQW, ESQT,
TLE, SMM, MMS, PTF


SPECIFICATIONS

For complete specifications and
recommended PCB layouts
see www.samtec.com?TSH**Insulator Material:**
Black Liquid Crystal Polymer
Terminal Material:
Phosphor Bronze**Plating:**
Sn or Au over
50 μ " (1.27 μ m) Ni**Operating Temp Range:**
-55 °C to +105 °C with Tin;
-55 °C to +125 °C with Gold
RoHS Compliant: Yes

Processing:

Lead-Free Solderable: Yes
SMT Lead Coplanarity:
(0.15 mm) .006" max

RECOGNITIONS

For complete scope of
recognitions see
www.samtec.com/quality**Note:** Some lengths, styles
and options are non-standard,
non-returnable.

ALSO AVAILABLE (MOQ Required)

- Other sizes and platings
Contact Samtec.

Mates with:

SQT, SQW, ESQT

SPECIFICATIONS

For complete specifications
see www.samtec.com?TMMS**Insulator Material:**
Black LCP
Terminal Material:
Phosphor Bronze**Plating:**
Sn or Au over
50 μ " (1.27 μ m) Ni**Operating Temp Range:**
-55 °C to +105 °C with Tin;
-55 °C to +125 °C with Gold
RoHS Compliant:
Yes**Lead-Free Solderable:** Yes

RECOGNITIONS

For complete scope of
recognitions see
www.samtec.com/quality**Note:** Some lengths, styles
and options are non-standard,
non-returnable.