

Rev. 5/5/2014

http://www.foxonline.com/need_a_sample.htm

**Need a
Sample®**

Resin Sealed SMD Crystal



Model: FQ1045A

RoHS Compliant / Pb Free

Rev. 5/5/2014

Page 2 of 2

http://www.foxonline.com/need_a_sample.htm



Need a
Sample®

• TAPE SPECIFICATIONS (millimeters)

MODEL	A	B	C	D	E	F	STD Reel QTY
FQ1045A	Ø1.5	4.0	8.0	11.5	24.0	2.0	1,000

• REEL SPECIFICATIONS (millimeters)

MODEL	G	H	I	J	K	L	M
FQ1045A	2.0	Ø13	Ø21	Ø100	Ø330	24.4	2.0



All specifications subject to change without notice.

• FQ1045A Standard Crystals

Part Number	Frequency	Tolerance	Stability	Temp Range	CL
FQ1045A-3.6864	3.686400	+/- 30 ppm	+/- 30 ppm	0 to +70 C	20pF
FQ1045A-4.000	4.000000	+/- 30 ppm	+/- 30 ppm	0 to +70 C	20pF
FQ1045A-6.000	6.000000	+/- 30 ppm	+/- 30 ppm	0 to +70 C	20pF
FQ1045AR-3.6864	3.686400	+/- 30 ppm	+/- 50 ppm	-40 to +85 C	20pF
FQ1045AR-4.000	4.000000	+/- 30 ppm	+/- 50 ppm	-40 to +85 C	20pF
FQ1045AR-6.000	6.000000	+/- 30 ppm	+/- 50 ppm	-40 to +85 C	20pF