


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT* PART NO.	DESCRIPTION	BUNDLE DIA.		A in. (mm)	B in. (mm)	C in. (mm)	D in. (mm)	F in. (mm)	MINIMUM LOOP TENSILE 2"/MIN. lbs. (N)	APPROX. WEIGHT lbs/(kg) per PACKAGE
		MIN. in. (mm)	MAX. in. (mm)							
DTKH	DURA-TY KIT 50' STRAPPING 25 HEADS	.020 (.51)	15' - 9" (4.8)	.331 (8.40)	.064 (1.63)	.393 (9.98)	.557 (14.15)	.824 (20.93)	200 (890)	0.85 (.386)
DTHH	BAG OF 25 HEADS	----- -----	----- -----	----- -----	----- -----	.393 (9.98)	.557 (14.15)	.824 (20.93)	----- -----	.15 (.068)
DTRH	50' REEL OF STRAPPING	.020 (.51)	15' - 9" (4.8)	.331 (8.40)	.064 (1.63)	----- -----	----- -----	----- -----	200 (890)	0.70 (.318)

* SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE

										DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS			
										PANDUIT CORP. TINLEY PARK, ILLINOIS			
										DURA-TY EXTRUDED CABLE TIES (HEAVY)			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
										DRAWN BY ERW		SCALE N/A	
										DATE 5/8/07		MAT'L; STRAP & HEAD - BLACK ACETAL EACH HEAD HAS TWO, TYPE 302 STAINLESS STEEL BARBS	
										CHK'D TGS		DRAWING NO. SS-27557	
										DWG A SIZE			
1	8/16/07	JABO		ADDED DTKH, DURA-TY KIT		SS-27557	1						
REV	DATE	BY	CHK	DESCRIPTION		ECN	R	CUST	SUP				