




WIRE RANGE	E13288	LR7189 Certified
12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED

- 1 STAMP AMP 12-10* APPROX AS SHOWN
- 2 WIRE INSUL, ø4.318-7.620[ø.170-.300]
- 3 BODY MATERIAL THK, 0.998±0.051[.039±.002]
- 4 APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.

1500	ON TAPE, REEL	2-35364-1
500	LOOSE PIECE	35364
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

MAX RECOMMENDED OPERATING
TEMPERATURE:

105°C [221°F]

VOLTAGE RATING:

300 V MAX

CIRCULAR MIL AREA:
2.63mm²-6.64mm²[5,180-13,100]
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.127[.005]
4 PLC ± -
ANGLES ± -

MATERIAL

BODY,SLV,COPPER PER ASTM B152
INSUL, PVC, COLOR, YELLOW

FINISH

BODY & SLV,TIN PLATE PER ASTM
B545

DWN
M ELLIS
17APR95

CHK
C PRESNELL
17APR95

APVD
N BIRCH
17APR95

PRODUCT SPEC
UL 486 A-B

APPLICATION SPEC
114-2157

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
TERMINAL, RING TONGUE, PIDG™
WIRE SIZE, 12-10 AWG

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-35364

RESTRICTED TO
-

SCALE
4:1

SHEET
1 OF 1

REV
G1