

151-00903

Standoff Tape Clip, Panel Thickness 0.02" - 0.23", PA66HIRHS, Natural, 3,000/box

Article Number: 151-00903

Part Number: 151-00903

Type: SOC10FT6LG

→Find a Distributor

→Order Samples

→Get Technical Drawings

    |  Share

→Base Data

Part No.	151-00903
Type	SOC10FT6LG
Color	Natural (NA)
Features	• Staggered fir tree branch design provides low insertion forces and high extraction forces. • Initial fir tree serves as a locating feature for assistance in blind assembly applications.
Application Method	They are fastened onto the tape bar using tape or cable ties.
Typical Application	Tape clips are designed to provide simple and easy methods of securing cable bundles, hoses, or pipes.

→Product Dimensions

Length (L)	2.3" / 58.0mm
Length (L2)	1.7" / 43.4mm
Width (W) (imperial)	0.6"
Width (W)	16.0mm
Height (H)	0.6" / 14.5mm
Max. Panel Thickness	0.23" / 6.0mm
Min. Panel Thickness	0.02" / 0.6mm
Min. Mounting Hole Ø	.24"
Max. Mounting Hole Ø	.27" / 6.9mm
Min. Mounting Hole Ø	6.1mm

→Material and Specifications

Material	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)
Flammability	UL94 HB
Operating Temperature	-40 °F to +230 °F (-40 °C to +110 °C)

→Logistic and Packaging

Packaging Type	box
Pkg. Qty.	3000
EAN code	4031026433127

[Find a Distributor](#)

[Get Product Samples](#)

[Get Technical Drawings](#)