


Housings

LB-System (side clip = 1 clip)

Top of Housings
cable entry from the side
straight cable entry


Bottom of Housings
surface mounted-/
socket-/cable-to-
cable housing



VS-System (locking system = 2 clips)

Top of Housings
cable entry from the side
straight cable entry

Bottom of Housings
surface mounted-/
socket-/cable-to-
cable housing



Description	Part No.	Width	Length	Height
1 HB.6.STS.1.16G	1-1102240-7	43.0	63.0	48.0
2 HB.6.STO.1.16G	1-1102243-7	43.0	60.0	48.0
3 HB.6.AG-LB	1-1102244-2	43.5	80.0	28.5
4 HB.6.AGD*-LB	1-1102245-2	43.5	83.0	28.5
4 HB.6.SG-LB.1.16Z	1-1102249-2	52.0	83.0	49.5
4 HB.6.SGD*-LB.1.16Z	1-1102253-2	52.0	82.0	49.5
5 HB.6.KDO-LB.1.16G	1-1102259-2	43.0	60.0	50.0
1 HD.16.STS.1.21G	1-1102461-7**	43.0	74.0	70.0
2 HD.16.STO.1.21G	1-1102467-7**	43.0	74.0	70.0
3 HD.16.SG-LB.1.21Z	1-1102472-2**	57.0	82.0	50.0
4 HD.16.SGD*-LB.1.21Z	1-1102480-2**	57.0	82.0	73.5
5 HD.16.KDO-LB.1.21G	1-1102489-2**	43.0	73.0	72.0


1 HB.10.STS-GR.1.16G	1-1102261-7	43.0	73.0	50.0
2 HB.10.STO-GR.1.16G	1-1102267-7	43.0	73.0	50.0
3 HB.10.AG-LB	1-1102271-2	43.5	93.0	28.5
3 HB.10.AGD*-LB	1-1102283-2	43.5	93.0	28.5
4 HB.10.SG-LB.1.16Z	1-1102274-2	52.0	94.0	53.5
4 HB.10.SGD*-LB.1.16Z	1-1102286-2	52.0	94.0	53.5
5 HB.10.KDO-LB.1.16G	1-1102279-2	43.0	73.0	55.5

1 HD.24.STS-GR.1.21G	1-1102496-7**	43.0	73.0	57.0
2 HD.24.STO-GR.1.21G	1-1102502-7**	43.0	73.0	70.0
3 HD.24.SG-LB.1.21Z	1-1102507-2**	57.0	94.0	73.5
4 HD.24.SGD*-LB.1.21Z	1-1102521-2**	57.0	94.0	73.5
5 HD.24.KDO-LB.1.21G	1-1102519-2**	43.0	73.0	72.0

6 HB.10.STS.1.16G	1-1102261-6	43.0	73.0	50.0
7 HB.10.STO.1.16G	1-1102267-6	43.0	73.0	50.0
8 HB.10.AG-VS	1-1102271-1	57.0	93.0	28.5
9 HB.10.SG-VS.1.16Z	1-1102276-1	57.0	94.0	55.5
10 HB.10.KDO-VS.1.16G	1-1102279-1	57.0	73.0	55.5

6 HD.24.STS.1.21G	1-1102496-6**	43.0	73.0	70.0
7 HD.24.STO.1.21G	1-1102502-6**	43.0	73.0	70.0
8 HD.24.SG-VS.1.21Z	1-1102507-1**	56.0	94.0	74.0
10 HD.24.KDO-VS.1.21G	1-1102515-1**	57.0	73.0	55.5

Contact Inserts



Description	Part No.	Screw	Crimp	Spring Clamp
1 HE.6.Sti.S	1-1103634-1	●		
HE.6.Bu.S	1-1103635-1	●		
HE.6.Sti.C	2-1103634-3		●	
HE.6.Bu.C	2-1103635-3		●	
HE.6.Sti.SC	7-1103634-1			●
HE.6.Bu.SC	7-1103635-1			●
2 HN.2D.24.Sti.C	2-1103200-3		●	
HN.2D.24.Bu.C	2-1103202-3		●	

3 HE.10.S6.S	1-1103636-1	●		
HE.10.Bu.S	1-1103637-1	●		
HE.10.Sti.C	2-1103636-3		●	
HE.10.Bu.C	2-1103637-3		●	
HE.10.Sti.SC	7-1103636-1			●
HE.10.Bu.SC	7-1103637-1			●
4 HN.2D.42.Sti.C	2-1103204-3		●	
HN.2D.42.Bu.C	2-1103206-3		●	