

Products

Products Overview

**Product Search**

Evaluate

- FAQ's

Design a Solution

- Part Drawings
- PDF-Right Angle ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Product Search >

Current refinements (click to remove) Search Tips

Part Number > DNFR14-250B-L

Your search criteria matched only one product, shown below

**DNFR14-250B-L**

- Right angle design for use in limited space applications
- Disconnect can be inserted and removed from the male tab without the use of tools for lower installed cost
- Disconnects available in common industry tab sizes
- Longer barrel design for use with Panduit standard disconnect tool



■ Part Number	DNFR14-250B-L
■ RoHS Compliancy Status	Compliant
■ Note	DNFR14-250B-L replaces DNFR14-250B-C
■ Part Description	Female Disconnect, right angle, nylon insulated, 16 – 14 AWG, .250 x .032 tab size.
■ Product Type	Disconnects
■ CSA Certified	Yes
■ UL Listed	Yes
■ Depth (In.)	0.63
■ Depth (mm)	16.0
■ Height (In.)	0.20
■ Height (mm)	5.1
■ Length (In.)	0.78
■ Length (mm)	19.8
■ Width (In.)	0.36
■ Width (mm)	9.1
■ CE Compliant	No
■ Max. Ins.	0.155
■ Max. Ins. (mm)	3.95
■ Panduit Color Code	Blue
■ Pricing Description	Female Disconnect, right angle, nylon insulated, 16 - 14 AWG, .250 x .032 tab size
■ Tab Size (In.)	0.250 x 0.032
■ Tab Size (mm)	6.3 x 0.8
■ Tool	CT-1525†, CT-2500†
■ Wire Range	16 – 14 AWG
■ Wire Range (mm²)	1.5 – 2.5
■ Min. Order UOM	PC
■ Min. Order Qty.	50
■ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
■ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.