

Housing - VC-MP-T4-R - 1855568

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Metal sleeve housing, powder-coating, locking screws with knurled head, type 4, cable screw connection Pg21

The illustration shows version VC-MP-T3-R



Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	401.82 GRM
Custom tariff number	85389099
Country of origin	Poland

Technical data

Dimensions

Height	75 mm
--------	-------

Ambient conditions

Degree of protection	IP65/IP66/IP67
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	When using fiber optics, the bending radii of the cable manufacturers must be observed.
Type	VC4
Degree of protection	IP65/IP66/IP67
Locking type	Screw locking, knurled head
Tightening torque, mounting screw	1 Nm $\pm$ 0.5 Nm
Type of the screw connection	1x Pg21
Pg screw connection	none
Cable exit	Angled

Housing - VC-MP-T4-R - 1855568

Technical data

General

Number of module slots	5
Housing material	Zinc die-cast
Housing surface material	Powder coating
Seal material	EPDM
Ambient temperature (operation)	-40 °C ... 125 °C

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27371205
eCl@ss 5.1	27371205
eCl@ss 6.0	27371205
eCl@ss 7.0	27371205
eCl@ss 8.0	27440202

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Drawings

Housing - VC-MP-T4-R - 1855568

Dimensioned drawing

