

Temperature and Humidity Datalogger

✓ **Datalogs up to 16,000 readings**
With USB interface for downloading to a PC

Features:

- Triple LCD displays Humidity, Temperature, and date (Year, Month, and Day)
- Programmable from keypad or PC
- Selectable data sampling rate
- User programmable audible and visual alarms
- Wall, desktop, or tripod mount
- Calibration via optional salt bottles
- Complete with Windows® compatible software, USB cable, Universal AC adaptor, and four AA batteries



Displays and logs the Humidity and Temperature levels in Production areas



Includes PC software for graphical or data report generation to further analyze the stored data.

Ordering Information:

42280Temperature and Humidity Datalogger
RH300-CAL33% and 75%RH Calibration Bottles
TR100Tripod

Specifications	Range	Basic Accuracy
Temperature	-4 to 144°F (-20 to 70°C)	±1°F/0.6°C
Humidity	0 to 100%	±3%
Dew Point	32 to 122°F (0 to 50°C)	
Memory	Temperature: 8,000 points; Humidity: 8,000 points	
Dimensions	4.75 x 3.5 x 1.5" (120.7 x 88.9 x 38.1mm)	
Weight	5.7oz (163g)	