


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE, AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.




ACTUAL SIZE




- MAX. BUNDLE DIA. 0.25 [6.4]

* PANDUIT PART NO.	WEIGHT LBS/100 PCS. (g)
VCC25	0.20 (91)



TEAR-TAB



TO APPLY CLIP:

1. REMOVE PROTECTIVE LINER.
2. PLACE IN DESIRED LOCATION.
3. APPLY PRESSURE TO CLIP.

NOTES:

- *1. SEE CURRENT PRICE SHEET FOR PART
NUMBER SUFFIX DESIGNATION FOR
PACKAGE SIZE.

-ADHESIVE TAPE: PRESSURE SENSITIVE FOAM
0.040 (1.02) THICK WITH ACRYLIC ADHESIVE
AND PROTECTIVE LINER. MOUNT IS DESIGNED
TO SUPPORT .25 lbs. (113g) MAXIMUM WEIGHT
ON A CLEAN, DRY, SMOOTH, GREASE-FREE SURFACE.

(DIMENSIONS IN BRACKETS ARE IN METRIC.)

CAD FILENAME/LAYERS

GB0146BA_PB_VCC25_A_02



CORP.

TINLEY PARK, ILLINOIS

VCC25-A
VERTICAL CORD CLIP

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.1 (2.5) (.XXX) ± 0.020 (.5)
(.XX) ± 0.05 (1.3) ANGLES $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY M. J. K.

MAT'L:	
--------	--

DATE	1-23-93
------	---------

NATURAL
NYLON

DRAWING NO.

1.5X

GB0146BA

DWG
A
SIZE

2	06/18/01	LGG		UPDATED FOR WEB	GB0146BA	2				
1	12-15-93	STR		DIMENSIONS ADDED	GB0146BA	1				
R	1-23-93	MJK		INITIAL RELEASE	GB0146BA	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		