

Screwdrivers, Nut Drivers & Accessories

Offering a variety of tip types, hex sizes, shaft lengths, and handle designs, Klein has the screwdrivers and nut drivers professionals demand to get the job done with comfort and ease of use.

F O R P r o f e s s i o n a l s . . . s i n c e 1 8 5 7 ®



Screwdrivers, Nut Drivers
& Accessories




Introduction – Screwdrivers, Nut Drivers & Accessories

Klein screwdrivers give professionals extra-quality features that have made the Klein name famous for hand tools – features that assure greater convenience, comfort and efficiency in use, plus exceptional strength and durability.

All Klein drivers are made of the highest quality tempered steel, carefully heat-treated for maximum strength. Shafts have integral flanges that provide an extra-strong, torque-proof anchor in the handle. Strong, durable black tips are forged and precision ground with square edges to fit screw openings securely. They resist slippage and provide positive turning action.

Cushion-Grip screwdrivers feature super-comfortable, sure-grip handles on top-quality blades for the professional. All Klein screwdrivers meet or exceed applicable ANSI and MIL specifications.



Using screwdrivers

The size of the screw and the type of opening it has determines which driver to use. But there are a few tips on how to use a driver that can be of benefit, because screwdrivers are the most often misused and abused hand tools of all.

1. **Never use a driver to do another tool's job.** Using a driver as a pry bar, scraper, or a chisel can ruin the tool, spoil the work and cause injury.
2. **Never push a driver beyond its capacity.** Make a pilot hole for the screw for easier driving. Use square-shank drivers for heavy work.
3. **Never expose a driver to excessive heat.** Direct flame can draw the temper from the metal, weakening and possibly warping it, making it unsafe and inefficient to use.

4. **Never use a driver at an angle to the screw.** Always keep the shank perpendicular to the screw head. Driving at an angle or using a point that is too small can spoil the screw or slip and damage the work.

5. **Never depend on a driver's handle or covered blade to insulate you from electricity.** Plastic and Cushion-Grip handles are intended only to provide a firm, comfortable grip. Insulated blades are intended only as a protective measure against shorting out components. Only use insulated tools that are marked with the official international 1000-volt rating symbol if there is any chance that the tool will make contact with an energized source.

6. **Discard damaged or worn drivers.**

TORX® is a registered trademark of Acument Intellectual Properties, LLC.

Journeyman™ Screwdriver Sets

Features:

JOURNEYMAN™

Sleek new tri-lobed handle features an ultra comfortable soft-grip material molded over a solid inner core to create exceptional control, grip, and balance.

Hex-shaped welded bolster offers additional strength between the blade and handle.

Precision-machined tip for exact fit into the fastener.

Exceptionally hard steel shaft efficiently transfers every bit of torque generated into the tip.



Meets or exceeds applicable ASME / ANSI specifications.

Patented Tip-Ident® quickly identifies the type of screwdriver and screwdriver tip orientation.



All dimensions are in inches and (millimeters).

⚠ WARNING: NOT insulated. Will NOT protect against electrical shock.

⚠ WARNING: Always wear approved eye protection.

⚠ WARNING: Do NOT use to pry or chisel.

5-Piece Journeyman™ Screwdriver Set

JOURNEYMAN

Additional Features:

- General purpose selection of the most frequently used screwdrivers.

Cat. No.	Set Contains	Weight (lbs.)		
JSDS01		1.15		
	Cat. No.	Description	Shaft Length	Overall Length
	JSD6C06	3/16" cabinet-tip screwdriver	6" (152 mm)	10-1/4" (260 mm)
	JSD4K08	1/4" keystone-tip screwdriver	4" (102 mm)	9" (228 mm)
	JSD6K09	5/16" keystone-tip screwdriver	6" (152 mm)	11" (279 mm)
	JSD4PH1	#1 Phillips-tip screwdriver	4" (102 mm)	8-1/4" (210 mm)
	JSD4PH2	#2 Phillips-tip screwdriver	4" (102 mm)	9" (228 mm)



JSDS01

7-Piece Journeyman™ Screwdriver Set

JOURNEYMAN

Additional Features:

- Accommodates a broad range of standard fastener sizes.

Cat. No.	Set Contains			Weight (lbs.)
JSDS02				1.65
Cat. No.	Description	Shaft Length	Overall Length	
JSD4C06	3/16" cabinet-tip screwdriver	4" (102 mm)	8-1/4" (210 mm)	
JSD6C06	3/16" cabinet-tip screwdriver	6" (152 mm)	10-1/4" (260 mm)	
JSD4K08	1/4" keystone-tip screwdriver	4" (102 mm)	9" (228 mm)	
JSD6K09	5/16" keystone-tip screwdriver	6" (152 mm)	11" (279 mm)	
JSD4PH1	#1 Phillips-tip screwdriver	4" (102 mm)	8-1/4" (210 mm)	
JSD4PH2	#1 Phillips-tip screwdriver	4" (102 mm)	9" (228 mm)	
JSD6PH3	#2 Phillips-tip screwdriver	6" (152 mm)	11" (279 mm)	



JSDS02

Journeyman™ Screwdrivers

Journeyman™ Cabinet-Tip Screwdrivers – Round Shaft

JOURNEYMAN

Additional Features:

- Narrow cabinet-tip permits blade access where space is limited.
- Exceptionally hard steel shaft efficiently transfers torque into the tip.



JSD6C06

Cat. No.	Shaft Tip Width	Shaft Length	Overall Length	Weight (lbs.)
JSD4C06	3/16" (5 mm)	4" (102 mm)	8-1/4" (210 mm)	0.15
JSD6C06	3/16" (5 mm)	6" (152 mm)	10-1/4" (260 mm)	0.15

All dimensions are in inches and (millimeters).

⚠ WARNING: Always wear approved eye protection.

⚠ WARNING: NOT insulated. Will NOT protect against electrical shock.

⚠ WARNING: Do NOT use to pry or chisel.



Journeyman™ Screwdrivers

Journeyman™ Phillips-Tip Screwdrivers – Round Shaft

JOURNEYMAN

Additional Features:

- Tips are precision machined to provide a consistent symmetry.
- Provides accurate fit and torque without slippage.



JSD4PH2

Cat. No.	Tip Size	Shaft Length	Overall Length	Weight (lbs.)
JSD4PH1	No. 1	4" (102 mm)	8-1/4" (210 mm)	0.15
JSD4PH2	No. 2	4" (102 mm)	9" (228 mm)	0.25
JSD6PH3	No. 3	6" (152 mm)	11" (279 mm)	0.35



Journeyman™ Keystone-Tip Screwdrivers – Round Shaft

JOURNEYMAN

Additional Features:

- The most popular flat tip style used in high torque applications.
- Hex bolster reinforces blade for hard use and shows for wrench assisted turning.




JSD6K09

Cat. No.	Shaft Tip Width	Shaft Length	Overall Length	Weight (lbs.)
JSD4K08	1/4" (6 mm)	4" (102 mm)	9" (228 mm)	0.25
JSD6K09	5/16" (8 mm)	6" (152 mm)	11" (279 mm)	0.35



Cushion-Grip Screwdriver Sets

Features:



All dimensions are in inches and (millimeters).

⚠ WARNING: NOT insulated. Will NOT protect against electrical shock.

⚠ WARNING: Always wear approved eye protection.

⚠ WARNING: Do NOT use to pry or chisel.



Cushion-Grip Screwdriver Sets

5-Piece Cushion-Grip Screwdriver Set

Additional Features:

- General-purpose selection of the most frequently used screwdrivers.
- Includes two cabinet-tip, one Phillips-tip and two keystone-tip screwdrivers.

Cat. No.	Set Contains			Weight (lbs.)
85075				1.30
	Cat. No.	Description	Blade Length	Overall Length
	600-4	square-shank, keystone-tip*	4" (102 mm)	8-11/32" (212 mm)
	601-6	round-shank, cabinet-tip	6" (152 mm)	9-3/4" (248 mm)
	602-6	round-shank, keystone-tip*	6" (152 mm)	10-15/16" (278 mm)
	603-4	round-shank, No. 2 Phillips-tip	4" (102 mm)	8-5/16" (211 mm)
	605-6	round-shank, cabinet-tip*	6" (152 mm)	10-11/32" (263 mm)

* Heavy-duty models



85075


7-Piece Cushion-Grip Screwdriver Set

Additional Features:

- General-purpose selection of the most frequently used screwdrivers.
- Includes three cabinet-tip, two Phillips-tip and two keystone-tip styles.

Cat. No.	Set Contains	Weight (lbs.)	
85076		1.50	
Cat. No.	Description	Blade Length	Overall Length
600-4	square-shank, keystone-tip*	4" (102 mm)	8-11/32" (212 mm)
602-6	round-shank, keystone-tip*	6" (152 mm)	10-15/16" (278 mm)
601-3	round-shank, cabinet-tip	3" (76 mm)	6-3/4" (171 mm)
601-6	round-shank, cabinet-tip	6" (152 mm)	9-3/4" (248 mm)
605-4	round-shank, cabinet-tip*	4" (102 mm)	8-11/32" (212 mm)
603-3	round-shank, No. 1 Phillips-tip	3" (76 mm)	6-3/4" (171 mm)
603-4	round-shank, No. 2 Phillips-tip	4" (102 mm)	8-5/16" (211 mm)

* Heavy-duty models



85076

7-Piece Multiple-Application Screwdriver Set

Additional Features:

- Specialty set for a wide variety of applications.
- Includes two cabinet-tip, one Phillips-tip, two keystone-tip, one rotary and one screw-holding screwdriver.

Cat.No.	Set Contains	Weight (lbs.)	
85077		1.65	
Cat. No.	Description	Blade Length	Overall Length
600-4	square-shank, keystone-tip*	4" (102 mm)	8-11/32" (212 mm)
601-6	round-shank, cabinet-tip	6" (152 mm)	9-3/4" (248 mm)
602-6	round-shank, keystone-tip*	6" (152 mm)	10-15/16" (278 mm)
603-4	round-shank, No. 2 Phillips-tip	4" (102 mm)	8-5/16" (211 mm)
605-6	round-shank, cabinet-tip*	6" (152 mm)	10-11/32" (263 mm)
670-6	cabinet-tip rotary screwdriver	6" (152 mm)	9-3/4" (248 mm)
K36	slotted screw-holding screwdriver	6" (152 mm)	9-3/4" (248 mm)

* Heavy-duty model



85077

All dimensions are in inches and (millimeters).

WARNING: Always wear approved eye protection.

WARNING: NOT insulated. Will NOT protect against electrical shock.

WARNING: Do NOT use to pry or chisel.

Screwdrivers, Nut Drivers & Accessories



Cushion-Grip Screwdriver Sets

7-Piece Multiple-Application Screwdriver & Nut Driver Set

Additional Features:

- Specialty set for a wide variety of applications.
- Includes one keystone-tip, two cabinet-tip, one Phillips-tip and three nut drivers.

Cat. No.	Set Contains			Weight (lbs.)
55152				2.00
Cat. No.	Description	Shank Length	Overall Length	
600-4	square-shank, keystone-tip*	4" (102 mm)	8-11/32" (212 mm)	
601-6	round-shank, cabinet-tip	6" (152 mm)	9-3/4" (248 mm)	
603-4	round-shank, No. 2 Phillips-tip	4" (102 mm)	8-5/16" (211 mm)	
605-6	round-shank, cabinet-tip*	6" (152 mm)	10-11/32" (263 mm)	
630-1/4	1/4" hex nut driver	3" (76 mm)	6-3/4" (171 mm)	
630-5/16	5/16" hex nut driver	3" (76 mm)	6-3/4" (171 mm)	
630-3/8	3/8" hex nut driver	3" (76 mm)	6-3/4" (171 mm)	

* Heavy-duty models



55152

8-Piece Cushion-Grip Screwdriver Set

Additional Features:

- General purpose selection of the most frequently used screwdrivers.
- Includes one cabinet-tip, three keystone-tip, four Phillips-tip styles.

Cat. No.	Set Contains			Weight (lbs.)
85078				1.65
	Cat. No.	Description	Shank Length	Overall Length
	600-1	round-shank, keystone-tip	1-1/2" (38 mm)	3-7/16" (87 mm)
	601-3	round-shank, cabinet-tip	3" (76 mm)	6-3/4" (171 mm)
	600-4	square-shank, keystone-tip*	4" (102 mm)	8-11/32" (212 mm)
	602-6	round-shank, keystone-tip*	6" (152 mm)	10-15/16" (278 mm)
	603-1	round-shank, No. 2 Phillips-tip	1-1/2" (38 mm)	3-7/16" (87 mm)
	603-3	round-shank, No. 1 Phillips-tip	3" (76 mm)	6-3/4" (171 mm)
	603-4	round-shank, No. 2 Phillips-tip	4" (102 mm)	8-5/16" (211 mm)
	603-6	round-shank, No. 3 Phillips-tip	6" (152 mm)	11" (279 mm)

* Heavy-duty models



85078

6-Piece Cushion-Grip Screwdriver Set

Additional Features:

- General-purpose selection of the most frequently used screwdrivers.
- Includes one cabinet-tip, two keystone-tip and three Phillips-tip styles.

Cat. No.	Set Contains			Weight (lbs.)
85074				1.50
	Cat. No.	Description	Blade Length	Overall Length
	601-3	round-shank, cabinet-tip	3" (76 mm)	6-3/4" (171 mm)
	600-4	square-shank, keystone-tip*	4" (102 mm)	8-11/32" (212 mm)
	600-6	square-shank, keystone-tip*	6" (152 mm)	10-15/16" (278 mm)
	603-3	round-shank, No. 1 Philips-tip	3" (76 mm)	6-3/4" (171 mm)
	603-4	round-shank, No. 2 Philips-tip	4" (102 mm)	8-5/16" (211 mm)
	603-6	round-shank, No. 3 Phillips-tip	6" (152 mm)	11" (279 mm)

* Heavy-duty models



85074

All dimensions are in inches and (millimeters).

WARNING: NOT insulated. Will NOT protect against electrical shock.

WARNING: Always wear approved eye protection.

WARNING: Do NOT use to pry or chisel.



Cushion-Grip Screwdriver Sets

4-Piece Cushion-Grip Screwdriver Set

Additional Features:

- The screwdrivers Professionals carry most often.
- Includes one Phillips-tip, two keystone-tip, one cabinet-tip screwdrivers.

NEW!

Cat. No.	Set Contains	Weight (lbs.)
85105		1.50

Cat. No.	Description	Blade Length	Overall Length
603-4	round-shank, No. 2 Phillips-tip	4" (102 mm)	8-5/16" (211 mm)
600-4	square-shank, keystone-tip*	4" (102 mm)	8-11/32" (212 mm)
601-6	round-shank, cabinet-tip	6" (152 mm)	9-3/4" (248 mm)
600-6	square-shank, keystone-tip*	6" (152 mm)	10-15/16" (278 mm)

* Heavy-duty models



85105



2-Piece 10" Long Blade Screwdriver Set

Additional Features:

- Phillips-tip is precision-machined to provide a more consistent geometric symmetry than conventional Phillips-tip screwdrivers.
- Precision-ground narrow cabinet-tip permits blade access where space is limited.
- Ideal for hard-to-reach places where added length is necessary.
- Includes one Phillips-tip and one cabinet-tip.



85072

Cat. No.	Set Contains	Weight (lbs.)
85072		.70

Cat. No.	Description	Shank Tip Size	Shank Length	Overall Length
603-10	round-shank, profilated Phillips-tip	No. 2	10" (254 mm)	14-5/16" (363 mm)
605-10	round-shank, cabinet-tip	1/4" (6 mm)	10" (254 mm)	14-5/16" (363 mm)



4-Piece Miniature Cushion-Grip Screwdriver Set

Additional Feature:

- Precision tips for exact fit and rigorous applications.

Cat. No.	Set Contains	Weight (lbs.)
85484		.14

Cat. No.	Tip Type Size	Shank Tip Size	Shank Length	Overall Length
604-3	Phillips-tip	No. 0	3" (76 mm)	5-3/4" (146 mm)
606-2	keystone-tip	1/16" (1.6 mm)	2" (51 mm)	4-3/4" (121 mm)
607-3	cabinet-tip	3/32" (2.4 mm)	3" (76 mm)	5-3/4" (146 mm)
608-3	cabinet-tip	1/8" (3.2 mm)	3" (76 mm)	5-3/4" (146 mm)



85484



All dimensions are in inches and (millimeters).

WARNING: NOT insulated. Will NOT protect against electrical shock.

WARNING: Always wear approved eye protection.

WARNING: Do NOT use to pry or chisel.

Screwdrivers, Nut Drivers & Accessories



Cushion-Grip Screwdriver Sets

4-Piece Square Recess Cushion-Grip Screwdriver Set

Additional Features:

- Color-coded handle ends with Tip-Ident® for quick and easy identification.
- Round shank with square-recess tip.
- Chrome-plated shank for corrosion resistance.
- Cushion-grip handle for greater torque and comfort.
- Works on most combination head receptacle, switch and panel screws.

Cat. No.	Set Contains	Weight (lbs.)
85664		1.50

Cat. No.	Point Size	Color Code	Shank Length	Overall Length
660	No. 0	yellow	4" (102 mm)	7-3/4" (197 mm)
661	No. 1	green	4" (102 mm)	7-3/4" (197 mm)
662	No. 2	red	4" (102 mm)	8-5/16" (211 mm)
663	No. 3	black	4" (102 mm)	8-5/16" (211 mm)



85664

5-Piece TORX® Cushion-Grip Screwdriver Set

Additional Features:

- Color-coded handle ends with Tip-Ident® for quick and easy identification.
- TORX® drive systems transmit more torque to the work and reduce slippage, saving fasteners.
- Chrome plated shank for corrosion resistance.
- Cushion-Grip handle for greater torque and comfort.

Cat. No.	Set Contains	Weight (lbs.)
19555		1.20

Cat. No.	TORX® Size	Color Code	Shank Length	Overall Length
19542	T15	yellow	4" (102 mm)	7-3/4" (197 mm)
19543	T20	green	4" (102 mm)	7-3/4" (197 mm)
19544	T25	blue	4" (102 mm)	7-3/4" (197 mm)
19545	T27	brown	4" (102 mm)	8-5/16" (211 mm)
19546	T30	red	4" (102 mm)	8-5/16" (211 mm)



19555

TORX® is a registered trademark of Acument Intellectual Properties, LLC.

2-Piece Stubby Screwdriver Set

Additional Feature:

- Double wings inside handle provide solid, twist-resistant blade anchor.



85071



Cat. No.	Set Contains	Weight (lbs.)
85071		.30

Cat. No.	Description	Shank Length	Overall Length
600-1	round-shank, keystone-tip	1-1/2" (38 mm)	3-7/16" (87 mm)
603-1	round-shank, Phillips-tip	1-1/2" (38 mm)	3-7/16" (87 mm)

Stubby Square-Recess Tip Cushion-Grip Screwdrivers

Additional Features:

- Double wings inside handle provide solid, twist-resistant blade anchor.
- Works on most combination head receptacle and switch screws.
- Color-coded handle ends for quick and easy identification.



85155

Cat. No.	Description	Color Code	Shank Length	Overall Length	Weight (lbs.)
668	round-shank, No. 1 square-recess tip	green	1-1/2" (38 mm)	3-7/16" (87 mm)	.15
669	round-shank, No. 2 square-recess tip	red	1-1/2" (38 mm)	3-7/16" (87 mm)	.15

Stubby Square-Recess Cushion-Grip Screwdriver Set

Cat. No.	Description	Color Code	Shank Length	Overall Length	Weight (lbs.)
85155	2-piece stubby square-recess cushion-grip screwdriver set	green (Cat. No. 668), red (Cat. No. 669)	1-1/2" (38 mm)	3-7/16" (87 mm)	.30

All dimensions are in inches and (millimeters).

WARNING: Always wear approved eye protection.

WARNING: NOT insulated. Will NOT protect against electrical shock.

WARNING: Do NOT use to pry or chisel.



Keystone-Tip Screwdrivers – Heavy-Duty Square-Shanks

Additional Features:

- Heavy-duty square shank for wrench-assisted turning.
- Bolster reinforces shank for hard use.
- Designed for the most demanding uses.

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
600-4	1/4" (6 mm)	4" (102 mm)	8-11/32" (212 mm)	.25
600-6	5/16" (8 mm)	6" (152 mm)	10-15/16" (278 mm)	.40
600-8	3/8" (10 mm)	8" (203 mm)	13-7/16" (341 mm)	.65
600-12	1/2" (13 mm)	12" (305 mm)	17-7/16" (443 mm)	.80



600-4

Keystone-Tip Screwdrivers – Heavy-Duty Round-Shanks

Additional Features:

- Built to handle the tough jobs with ease.
- Hex bolster reinforces shank for hard use and allows wrench assisted turning.

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
600-1*	1/4" (6 mm)	1-1/2" (38 mm)	3-7/16" (87 mm)	.10
602-3	7/32" (6 mm)	3" (76 mm)	6-3/4" (171 mm)	.15
602-4	1/4" (6 mm)	4" (102 mm)	8-11/32" (212 mm)	.25
602-6	5/16" (8 mm)	6" (152 mm)	10-15/16" (278 mm)	.35
602-8	3/8" (10 mm)	8" (203 mm)	13-7/16" (341 mm)	.55
602-10	3/8" (10 mm)	10" (254 mm)	15-7/16" (392 mm)	.60
602-12	3/8" (10 mm)	12" (305 mm)	17-7/16" (443 mm)	.65



602-6

* Bolster not available on 600-1.
Refer to the insulated section for insulated screwdrivers.

Cabinet-Tip Screwdrivers – Round-Shanks

Additional Feature:

- Narrow cabinet-tip permits blade access where space is limited.

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
601-3	3/16" (5 mm)	3" (76 mm)	6-3/4" (171 mm)	.10
601-4	3/16" (5 mm)	4" (102 mm)	7-3/4" (197 mm)	.15
601-6	3/16" (5 mm)	6" (152 mm)	9-3/4" (248 mm)	.15
601-8	3/16" (5 mm)	8" (203 mm)	11-3/4" (298 mm)	.20
601-10	3/16" (5 mm)	10" (254 mm)	13-3/4" (349 mm)	.20



601-6

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
Heavy-Duty Shanks				
605-4	1/4" (6 mm)	4" (102 mm)	8-11/32" (212 mm)	.25
605-6	1/4" (6 mm)	6" (152 mm)	10-11/32" (263 mm)	.30
605-8	1/4" (6 mm)	8" (203 mm)	12-11/32" (314 mm)	.30
605-10	1/4" (6 mm)	10" (254 mm)	14-11/32" (365 mm)	.35

Refer to the insulated section for insulated screwdrivers.

Profilated Phillips-Tip Screwdrivers – Round-Shanks

Additional Features:

- Tips are precision-machined to provide a more consistent geometric symmetry than conventional Phillips-tip screwdrivers.
- Provides accurate fit and torque without slippage.



603-7

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
603-1	No. 2	1-1/2" (38 mm)	3-7/16" (87 mm)	.10
603-3	No. 1	3" (76 mm)	6-3/4" (171 mm)	.15
603-4	No. 2	4" (102 mm)	8-5/16" (211 mm)	.25
603-6	No. 3	6" (152 mm)	11" (279 mm)	.35
603-7	No. 2	7" (178 mm)	11-5/16" (287 mm)	.30
603-10	No. 2	10" (254 mm)	14-5/16" (364 mm)	.35

Refer to the insulated section for insulated screwdrivers.

All dimensions are in inches and (millimeters).

WARNING: Always wear approved eye protection.

WARNING: NOT insulated. Will NOT protect against electrical shock.

WARNING: Do NOT use to pry or chisel.



Cushion-Grip Screwdrivers

Miniature Cushion-Grip Screwdrivers



Additional Feature:

- Precision tip for exact fit and rigorous applications.

Cat. No.	Tip Type	Tip Size	Shank Length	Overall Length	Weight (lbs.)
604-3	Phillips-tip	No. 0	3" (76 mm)	5-3/4" (146 mm)	.04
606-2	keystone-tip	1/16" (1.6 mm)	2" (51 mm)	4-3/4" (121 mm)	.03
607-2	cabinet-tip	3/32" (2.4 mm)	2" (51 mm)	4-3/4" (121 mm)	.03
607-3	cabinet-tip	3/32" (2.4 mm)	3" (76 mm)	5-3/4" (146 mm)	.04
607-4	cabinet-tip	3/32" (2.4 mm)	4" (102 mm)	6-3/4" (171 mm)	.04
608-2	cabinet-tip	1/8" (3.2 mm)	2" (51 mm)	4-3/4" (121 mm)	.03
608-3	cabinet-tip	1/8" (3.2 mm)	3" (76 mm)	5-3/4" (146 mm)	.04
608-4	cabinet-tip	1/8" (3.2 mm)	4" (102 mm)	6-3/4" (171 mm)	.05
608-6	cabinet-tip	1/8" (3.2 mm)	6" (152 mm)	8-3/4" (222 mm)	.05
608-8	cabinet-tip	1/8" (3.2 mm)	8" (203 mm)	10-3/4" (273 mm)	.05
608-10	cabinet-tip	1/8" (3.2 mm)	10" (254 mm)	12-3/4" (324 mm)	.05

Square-Recess Tip Screwdrivers – Round-Shanks



Additional Features:

- Color-coded handle ends for quick and easy identification.
- Round shank with Square-Recess tip.
- Chrome plated shank for corrosion resistance.

Cat. No.	Tip Size	Color Code	Shank Length	Overall Length	Weight (lbs.)
660	No. 0	yellow	4" (102 mm)	7-3/4" (197 mm)	.20
661	No. 1	green	4" (102 mm)	7-3/4" (197 mm)	.20
662	No. 2	red	4" (102 mm)	8-1/4" (210 mm)	.30
663	No. 3	black	4" (102 mm)	8-1/4" (210 mm)	.30
665	No. 1	green	8" (203 mm)	11-3/4" (298 mm)	.30
666	No. 2	red	8" (203 mm)	12-1/4" (311 mm)	.40
667	No. 3	black	8" (203 mm)	12-1/4" (311 mm)	.40

Refer to the insulated section for insulated screwdrivers.

Terminal Block Screwdriver

NEW!

Additional Features:

- Precision-machined tip provides exact fit for terminal block screws.
- Tip is up to 19% stronger than competitors.
- Tip provides 76% higher torque value than the required ASME B107 Standard.
- Cushion-Grip handle offers greater torque comfort.

Cat. No.	Shank Top Width	Shank Length	Overall Length	Weight (lbs.)
612-4	1/8" (3.2 mm)	4" (100 mm)	7-3/4" (200 mm)	0.15

All dimensions are in inches and (millimeters).

WARNING: Always wear approved eye protection.

Coated Cabinet-Tip Screwdrivers – Round-Shanks



Additional Features:

- Plastic coated for circuit protection only. NOT INSULATED.
- Special plastic coating resists cutting, cracking and chipping.
- Thin coating permits use in confined areas.

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
620-3	3/16" (5 mm)	3" (76 mm)	6-3/4" (171 mm)	.15
621-6	3/16" (5 mm)	6" (152 mm)	9-3/4" (248 mm)	.20
621-8	3/16" (5 mm)	8" (203 mm)	11-3/4" (298 mm)	.20
621-10	3/16" (5 mm)	10" (254 mm)	13-3/4" (349 mm)	.25
Heavy-Duty Shanks				
620-4	1/4" (6 mm)	4" (102 mm)	8-11/32" (212 mm)	.20
620-6	5/16" (8 mm)	6" (152 mm)	10-15/16" (278 mm)	.40
620-8	3/8" (10 mm)	8" (203 mm)	13-7/16" (341 mm)	.60

TORX® Screwdrivers – Round-Shanks



Additional Features:

- Color-coded handle ends for quick and easy identification.
- TORX® tip drive cuts slippage, saves fasteners and transmits more torque to the work.
- Chrome-plated shank for corrosion resistance.

Cat. No.	TORX® Size	Color Code	Shank Length	Overall Length	Weight (lbs.)
19542	T15	yellow	4" (102 mm)	8-5/16" (211 mm)	.20
19543	T20	green	4" (102 mm)	8-5/16" (211 mm)	.25
19544	T25	blue	4" (102 mm)	8-5/16" (211 mm)	.25
19545	T27	brown	4" (102 mm)	8-5/16" (211 mm)	.25
19546	T30	red	4" (102 mm)	8-5/16" (211 mm)	.25

TORX® is a registered trademark of Acument Intellectual Properties, LLC.



WARNING: NOT insulated. Will NOT protect against electrical shock.

WARNING: Do NOT use to pry or chisel.



Cushion-Grip Screwdrivers

Conduit-Fitting and Reaming Screwdriver

Additional Features:

- Hooded-blade design keeps tip from slipping out of screws, especially when tightening hard-to-reach conduit fittings. Thicker hood is designed for rugged use.
- Reams and smooths 1/2" (13 mm), 3/4" (19 mm), and 1" (25 mm) thin-wall conduit ends to protect wire and permit correct installation of fittings.
- Reams both the inside and outside of the conduit at the same time.
- Longer Cushion-Grip handle provides comfort and more torque for reaming.
- Replaceable reaming blade is now held in place with a 1/16" set screw.



Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
85191	5/16" (8 mm)	2-1/2" (64 mm)	7-1/2" (191 mm)	.50
19353	conduit reamer replacement blade kit			.01

Conduit Reamer

- Locks onto screwdrivers; reams and smooths thin-wall conduit.
- Reams ID and OD at the same time.
- Two set-screws for round- and square-shank screwdrivers.



Cat. No.	Conduit Capacity	Weight (lbs.)
19352	1/2", 3/4", 1"	.20
19353	conduit reamer replacement blade kit for 19352	.01
19351	conduit reamer replacement blade for 19350	.01

- Fits up to 3/8" (10 mm) keystone-tip screwdrivers.
- NOT for use on power tools.


Rapi-Drive® Screwdrivers

Cabinet-Tip Screwdrivers – Rapi-Drive®

Additional Features:

- Crank-action handle spins screws fast with one hand.
- Saves time and effort, especially on long-threaded screws in switch plates, light fixtures, etc.

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
670-3	3/16" (5 mm)	4" (102 mm)	7-3/4" (197 mm)	.15
670-6	3/16" (5 mm)	6" (152 mm)	9-3/4" (248 mm)	.20
671-6	1/4" (6 mm)	6" (152 mm)	9-3/4" (248 mm)	.20




Phillips Screwdrivers – Rapi-Drive®

Additional Features:

- Crank-action handle spins screws fast with one hand.
- Saves time and effort, especially on long-threaded screws in switch plates, light fixtures, etc.

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
681-6	No. 1	6" (152 mm)	9-3/4" (248 mm)	.20
682-6	No. 2	6" (152 mm)	9-3/4" (248 mm)	.25




Square-Recess Screwdrivers – Rapi-Drive®

Additional Features:

- Crank-action handle spins screws fast with one hand.
- Color-coded handle ends for quick and easy identification.

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
691-6	No. 1	6" (152 mm)	9-3/4" (248 mm)	.35
692-6	No. 2	6" (152 mm)	9-3/4" (248 mm)	.35



All dimensions are in inches and (millimeters).

⚠ WARNING: Always wear approved eye protection.

⚠ WARNING: NOT insulated. Will NOT protect against electrical shock.

⚠ WARNING: Do NOT use to pry or chisel.



Rapi-Driv® Screwdrivers

Interchangeable Rapi-Driv®

- The original Klein Cushion-Grip handle for superior comfort and torque!
- Interchangeable bit holder allows quick switching between tip styles and works with other standard size bits.
- Crank-action handle allows you to spin screws fast with one hand.
- Blast finish bit provides firm grip on fasteners to reduce cam out.


Cat. No.	Contains	Shaft Length	Overall Length	Weight (lbs.)
67100	3/16" slotted, #2 Phillips	6" (152 mm)	9-3/4" (248 mm)	.26

2-in-1 Replacement Bit

Cat. No.	Fits	Description	Quantity	Weight (lbs.)
67101	2-in-1 Rapi-Driv®, 10-in-1, 11-in-1 and 10-Fold™	3/16" slotted, #2 Phillips replacement bit	contains 2 bits	.012



67100



Specialty Screwdrivers

Slotted Screw-Holding Screwdrivers

Additional Features:

- Starts and drives screws with one hand when working in hard-to-reach spaces.
- Cushion-Grip handle provides superior torque and comfort with non-slip grip.

Cat. No.	Screwdriver Type	Shank Length	Overall Length	Weight (lbs.)
32215	1/4" cabinet	7" (178 mm)	11-1/4" (276 mm)	0.32
32216	#2 Phillips	7" (178 mm)	11-1/4" (276 mm)	0.32



32215



NEW!

Wire Bending Cabinet-Tip Screwdrivers – Round-Shank

Additional Feature:

- Metal stud offers a convenient and easy way to bend, loop and connect solid wire when installing outlets and switches.

Cat. No.	Tip Size	Shank Length	Overall Length	Bends AWG Gauges	Finish	Weight (lbs.)
605-4B	1/4" (6 mm)	4" (102 mm)	8-11/32" (212 mm)	Nos. 10, 12, 14	chrome-plated	0.25
605-6B	1/4" (6 mm)	6" (152 mm)	10-11/32" (263 mm)	Nos. 10, 12, 14	chrome-plated	0.30



605-6B



Wire Bending Phillips-Tip Screwdrivers – Round-Shanks

Additional Feature:

- Metal stud offers a convenient and easy way to bend, loop and connect solid wire when installing outlets and switches.

Cat. No.	Tip Size	Shank Length	Overall Length	Bends AWG Gauges	Finish	Weight (lbs.)
603-3B	No. 1	3" (76 mm)	6-3/4" (171 mm)	Nos. 12 and 14	chrome-plated	0.15
603-4B	No. 2	4" (102 mm)	8-5/16" (211 mm)	Nos. 10, 12, 14	chrome-plated	0.25



603-4B



Wire Bending Square-Recess Tip Screwdrivers – Round Shanks

Additional Feature:

- Metal stud offers a convenient and easy way to bend, loop and connect solid wire when installing outlets and switches.

Cat. No.	Tip Size	Shank Length	Overall Length	Bends AWG Gauges	Finish	Weight (lbs.)
661B	No. 1	4" (102 mm)	8-1/4" (210 mm)	Nos. 10, 12, 14	chrome-plated	0.20
662B	No. 2	4" (102 mm)	8-1/4" (210 mm)	Nos. 10, 12, 14	chrome-plated	0.30



661B



All dimensions are in inches and (millimeters).

⚠WARNING: NOT insulated. Will NOT protect against electrical shock.

⚠WARNING: Always wear approved eye protection.

⚠WARNING: Do NOT use to pry or chisel.



Multi-Bit Screwdrivers/Nut Drivers

Heavy-Duty Multi-Bit Screwdriver/Nut Driver

- Klein's Heavy-Duty Multi-Bit driver has improved design and construction for greater strength and Cushion-Grip handles for superior torque and comfort.
- Shaft holds 6 universal tips; converts to 3 nut driver sizes and 1 hex driver
- Strong, heat-treated nut drivers for improved torque



32557

Cat. No.	Shaft Length	Overall Length	Weight
32557	2.95" (75 mm)	7.9" (201 mm)	0.48

NEW!

Ratcheting Multi-Bit Screwdriver/Nut Driver

- Klein's Heavy-Duty Ratcheting Multi-Bit driver provides high-torque capability and comfortable Cushion-Grip handles.
- Shaft holds 6 universal tips; converts to 3 nut driver sizes and 1 hex driver
- Strong, heat-treated nut drivers for improved torque
- 3-way ratcheting mechanism for forward, reverse and locked positions



32558

Cat. No.	Shaft Length	Overall Length	Weight
32558	2.95" (75 mm)	8.0" (203 mm)	0.71

NEW!

Extended-Reach Multi-Bit Screwdrivers/Nut Drivers

- Klein's Extended-Reach Multi-Bit drivers have extended shafts and blades that provide 39% longer reach, and Cushion-Grip handles for superior torque and comfort.
- Shaft holds 4 universal tips and converts to 2 nut driver sizes
- Extra-long shaft provides full reach of 4" standard-blade screwdriver
- Small diameter shaft for comfortable grip and quick, easy turning



Cat. No. 32560



Cat. No. 32559



32559

Cat. No.	Shaft Length	Overall Length	Weight
32559	4.11" (104 mm)	9.1" (231 mm)	0.41
32560	4.11" (104 mm)	9.1" (231 mm)	0.41

NEW!

Stubby Multi-Bit Screwdriver/Nut Driver

- Klein's Stubby Multi-Bit driver allows you to work in tight spaces.
- Shaft holds 4 universal tips and converts to 2 nut driver sizes
- Compact design features standard 1-1/4" shaft



Cat. No.	Shaft Length	Overall Length	Weight
32561	1.27" (32 mm)	3.2" (81 mm)	0.16

NEW!



32561

All dimensions are in inches and (millimeters).

WARNING: NOT insulated. Will NOT protect against electrical shock.

WARNING: Always wear approved eye protection.

WARNING: Do NOT use to pry or chisel.



Multi-Bit Screwdrivers/Nut Drivers

5-in-1 Screwdriver/Nut Driver

Additional Feature:

- End of handle is marked to quickly identify tool.



32476

Cat. No.	Contains	Weight (lbs.)
32476	5/16" nut driver, #1 and #2 Phillips, 9/32" slotted and 3/16" slotted	.35

10-in-1 Screwdriver/Nut Driver

Additional Feature:

- End of handle is marked to quickly identify tool.



TORX® is a registered trademark of Acument Intellectual Properties, LLC.



32477

Cat. No.	Contains	Weight (lbs.)
32477	5/16" and 1/4" nut drivers, #1 and #2 Phillips, 1/4" and 3/16" slotted, T10 and T15 TORX®, #1 and #2 square-recess	.35

11-in-1 Screwdriver/Nut Driver

Additional Feature:

- Integrated screwdriver/nut driver shaft holds 8 popular tips and converts to 3 nut driver sizes.
- End of handle is marked to quickly identify tool.



TORX® is a registered trademark of Acument Intellectual Properties, LLC.



32500

Cat. No.	Contains	Weight (lbs.)
32500	3/8", 5/16" and 1/4" nut drivers, #1 and #2 Phillips, 1/4" and 3/16" slotted, T10 and T15 TORX®, #1 and #2 square-recess	.44

11-in-1 Screwdriver/Nut Driver with Schrader® Valve Removal/ Installation Bit

Additional Features:

- Versatile 11-in-1 tool for the professional.
- Includes unique style bit for installation/removal of common TR-4 Schrader® valves and aggressive thread extractor tip for backing out broken cores.
- Great for HVAC and other industrial applications.
- Cushion-Grip handle for superior torque and comfort.



Schrader® is a registered trademark of Schrader International, Inc.



32527

Cat. No.	Contains	Weight (lbs.)
32527	3/8", 5/16" and 1/4" nut drivers, #1 and #2 Phillips, #1 square and #2 square, 1/4" and 3/16" slotted, Schrader® valve core removal/installation – extractor	.44

10-in-1 Folding Screwdriver/Nut Driver

10-FOLD®

- Conveniently folds up for easy storage or to fit into your pocket.
- Each driver arm contains four interchangeable bit styles and two nut drivers.
- Unfold each driver arm up to a full 180° for straight on driving power, or at 90° for extra leverage on stubborn fasteners.
- The quick release button easily unlocks a fully extended driver arm.



32535

TORX®	TAMPERPROOF TORX®	FRACTIONAL HEX	METRIC HEX
32536	32537	32538	32539

TORX® is a registered trademark of Acument Intellectual Properties, LLC.

Cat. No.	Handle Color	Description	Weight (lbs.)
32535	black	5/16" & 1/4" nut drivers, #1 and #2 Phillips, 1/4" & 3/16" slotted, T10 & T15 TORX®, and #1 and #2 square-recess	0.37
32536	green	5/16" & 1/4" nut drivers, T6, T7, T8, T10, T15, T20, T25, T27 TORX®	0.37
32537	green	5/16" & 1/4" nut drivers, T7, T8, T9, T10, T15, T20, T25, T27 TORX®	0.37
32538	red	5/16" & 1/4" nut drivers, 1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16" standard hex	0.37
32539	blue	5/16" & 1/4" nut drivers, .9 mm, 1.3 mm, 1.5 mm, 2 mm, 2.5 mm, 3 mm, 4 mm, 5 mm metric hex	0.37

All dimensions are in inches and (millimeters).

WARNING: NOT insulated. Will NOT protect against electrical shock.

WARNING: Always wear approved eye protection.

WARNING: Do NOT use to pry or chisel.



Replacement Parts Multi-Bit Screwdriver/Nut Drivers

Replacement Bits for Screwdriver/Nut Drivers

- Precision-machined tips for exact fit into fastener.



32484



32482



32483

Replacement Bits for Multi-Bit Interchangeable Screwdriver/Nut Drivers (32557, 32558, 32559, 32560, 32561)

Cat. No.	Fits	Description	Quantity
32392	32557 and 32558	Heavy Duty Main Blade Barrel	contains 1 unit
32394	32557 and 32558	Heavy Duty Secondary Blade Barrel	contains 2 units
32395	32559 and 32560	Extended Blade Barrel	contains 1 unit
32396	32561	Stubby Blade Barrel	contains 1 unit
32397	32557 and 32558	Screwdriver Bit & #2 PH x #1 Square	contains 2 bits
32398	32557, 32558 and 32561	Screwdriver Bit & #1 PH x 1/4 Slotted	contains 2 bits
32399	32557 and 32558	Screwdriver Bit & #2 Square x 3/16 Slotted	contains 2 bits
32400	32559	Extended Screwdriver Bit & #2 PH x #1 PH	contains 2 bits
32401	32559	Extended Screwdriver Bit & 3/16 Slotted x 1/4 Slotted	contains 2 bits
32410	32560	Extended Screwdriver Bit & #2 Square x #2 PH	contains 2 bits
32411	32560	Extended Screwdriver Bit & #1 Square x 1/4 Slotted	contains 2 bits
32412	32561	Screwdriver Bit & #2 PH x 3/16 Slotted	contains 2 bits

Replacement Bits for 5-in-1 Interchangeable Screwdriver/Nut Drivers

Cat. No.	Fits	Description	Quantity
32478	5-in-1 (Cat. No. 32476)	#1 Phillips – 3/16" slotted	contains 1 bit
32479	5-in-1 (Cat. No. 32476)	#2 Phillips – 9/32" slotted	contains 1 bit

Replacement Bits for 10-in-1, 11-in-1 and 10-Fold® Interchangeable Screwdriver/Nut Drivers

Cat. No.	Fits	Description	Quantity
32482	10-in-1, 11-in-1 and 10-Fold™	#1 Phillips & 3/16" Slotted	contains 2 bits
32483	10-in-1, 11-in-1 and 10-Fold™	#2 Phillips & 1/4" Slotted	contains 2 bits
32484	10-in-1, 11-in-1 and 10-Fold™	#1 Square & #2 Square	contains 2 bits
67101	10-in-1, 11-in-1 and 10-Fold™	#2 Phillips & 3/16" Slotted	contains 2 bits
32540	10-in-1, 11-in-1 and 10-Fold™	TT7 & TT8 Tamperproof TORX®	contains 2 bits
32541	10-in-1, 11-in-1 and 10-Fold™	TT9 & TT10 Tamperproof TORX®	contains 2 bits
32542	10-in-1, 11-in-1 and 10-Fold™	TT15 & TT20 Tamperproof TORX®	contains 2 bits
32543	10-in-1, 11-in-1 and 10-Fold™	TT25 & TT27 Tamperproof TORX®	contains 2 bits
32544	10-in-1, 11-in-1 and 10-Fold™	#6 TORX® & #7 TORX®	contains 2 bits
32485	10-in-1, 11-in-1 and 10-Fold™	#10 TORX® & #15 TORX®	contains 2 bits
32545	10-in-1, 11-in-1 and 10-Fold™	#T8 TORX® & #10 TORX®	contains 2 bits
32546	10-in-1, 11-in-1 and 10-Fold™	#T25 TORX® & #T27 TORX®	contains 2 bits
32547	10-in-1, 11-in-1 and 10-Fold™	3/32" Hex & 7/64" Hex	contains 2 bits
32548	10-in-1, 11-in-1 and 10-Fold™	5/32" Hex & 3/16" Hex	contains 2 bits
32549	10-in-1, 11-in-1 and 10-Fold™	1/16" Hex & 5/64" Hex	contains 2 bits
32550	10-in-1, 11-in-1 and 10-Fold™	1/8" Hex & 9/64" Hex	contains 2 bits
32551	10-in-1, 11-in-1 and 10-Fold™	.9 mm Hex & 1.3 mm Hex	contains 2 bits
32552	10-in-1, 11-in-1 and 10-Fold™	1.5 mm Hex & 2 mm Hex	contains 2 bits
32553	10-in-1, 11-in-1 and 10-Fold™	2.5 mm Hex & 3 mm Hex	contains 2 bits
32554	10-in-1, 11-in-1 and 10-Fold™	4 mm Hex & 5 mm Hex	contains 2 bits

TORX® is a registered trademark of Acument Intellectual Properties, LLC.

All dimensions are in inches and (millimeters).

⚠ WARNING: Always wear approved eye protection.

⚠ WARNING: NOT insulated. Will NOT protect against electrical shock.

⚠ WARNING: Do NOT use to pry or chisel.

Screwdrivers, Nut Drivers
& Accessories



Multi-Bit Screwdrivers/Nut Drivers

Non-Ratcheting Magnetic Screwdriver with 32-Piece Tamperproof Bit Set

- Cushion-Grip handle for superior torque and comfort.
- Sturdy bit and screw holding magnet allows for screws to fit securely in place for easy use.
- Includes complete tamperproof bit set in block.



32510

Cat. No.	Set Contains	Weight (lbs.)
32510		.71

Bits Included


TORX® – T7, T8, T10, T15, T20, T25, T27, T30 and T40
 Fraction Hex – 3/32", 7/64", 1/8", 9/64", 5/32", and 3/16"
 Metric Hex – 2 mm, 2.5 mm, 3 mm, 4 mm, and 5 mm
 Spanner – 4, 6, 8, and 10
 Tri-Wing® – 1, 2, 3 and 4
 TORQ-SET® – 6, 8 and 10
 1/4" square to 1/4" hex adapter to drive sockets

TORX® is a registered trademark of Acument Intellectual Properties, LLC. TORQ-SET® and Tri-Wing® are registered trademarks of Phillips Screw Co.

Magnetic Screwdriver Bit Sets

32-Piece Standard Tip Bit Set

- Durable PVC black block allows for easy storage of standard bits.
- Block slides over most screwdriver shafts for easy bit access and storage.
- Industrial strength, heat-treated steel bits for long lasting use.



32526

Cat. No.	Set Contains	Weight (lbs.)
32526		.425

Bits Included

Hex – 5/64", 3/32", 7/64", 1/8", 9/64", 5/32" and 3/16"
 Phillips – #0, #1, #2 (Qty. 3), and #3
 Square Recess – #1, #2, and #3
 TORX® – T6, T7, T8, T10, T15, T20 and T25
 Slotted – 3-4, 5-6, 6-8, 8-10, 10-12, 12-14 screw sizes
 Clutch – 5/32" and 3/16"
 1/4" square to 1/4" hex adapter to drive sockets

TORX® is a registered trademark of Acument Intellectual Properties, LLC. TORQ-SET® and Tri-Wing® are registered trademarks of Phillips Screw Co.

32-Piece Tamperproof Tip Bit Set

- Durable PVC gray block allows for easy storage of tamperproof bits.
- Block slides over most screwdriver shafts for easy bit access and storage.
- Industrial strength, heat-treated steel bits for long lasting use.



32525

Cat. No.	Set Contains	Weight (lbs.)
32525		.425

Bits Included

TORX® – T7, T8, T10, T15, T20, T25, T27, T30 and T40
 Fraction Hex – 3/32", 7/64", 1/8", 9/64", 5/32", and 3/16"
 Metric Hex – 2 mm, 2.5 mm, 3 mm, 4 mm, and 5 mm
 Spanner – 4, 6, 8, and 10
 Tri-Wing® – 1, 2, 3 and 4
 TORQ-SET® – 6, 8 and 10
 1/4" square to 1/4" hex adapter to drive sockets

All dimensions are in inches and (millimeters).

WARNING: Always wear approved eye protection.

WARNING: NOT insulated. Will NOT protect against electrical shock.

WARNING: Do NOT use to pry or chisel.



Features:

Handle size and shape provide greater contact area with hand for maximum turning power and a more comfortable grip.

Patented, oil-resistant, anti-slip, plastic flock on handle helps prevent slippage.



Special high-alloy steel for exceptionally strong blade and long life.

Triangular-shaped handle for more turning power.

Rounded end virtually eliminates pressure points in the palm of the hand.

Grip-It® Keystone-Tip Screwdrivers – Hex-Shanks

Additional Feature:

- Hex-shaped bolster and shaft for wrench-assisted turning

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
19435	7/32" (5.5 mm)	3-15/16" (100 mm)	8-1/16" (205 mm)	.20
19436	5/16" (8 mm)	5-7/8" (150 mm)	10-13/16" (275 mm)	.35



19435

Grip-It® Keystone-Tip Screwdrivers – Round-Shanks

Additional Feature:

- Hex-shaped bolster for wrench-assisted turning.

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
19427	7/32" (5.5 mm)	3-15/16" (100 mm)	8-1/16" (205 mm)	.15
19428	5/16" (8 mm)	5-7/8" (150 mm)	10-13/16" (275 mm)	.30



19427

Grip-It® Cabinet-Tip Screwdrivers – Round-Shanks

Additional Feature:

- Narrow cabinet-tip permits blade access where space is limited.

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
19405	7/32" (5.5 mm)	3-15/16" (100 mm)	7-11/16" (195 mm)	.15



19405

Grip-It® Profilated Phillips-Tip Screwdrivers – Round-Shanks

Additional Features:

- Tips are precision machined to provide a more consistent geometric symmetry than conventional Phillips-tip screwdrivers.
- Provides accurate fit and torque without slippage.

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
19445	No. 1	3-1/8" (80 mm)	6-7/8" (175 mm)	.10
19446	No. 2	3-15/16" (100 mm)	8-1/16" (205 mm)	.15



19446

All dimensions are in inches and (millimeters).

⚠ WARNING: NOT insulated. Will NOT protect against electrical shock.

⚠ WARNING: Always wear approved eye protection.

⚠ WARNING: Do NOT use to pry or chisel.



Plastic-Handle Screwdriver Set

Features:

Meets or exceeds applicable ASME / ANSI specifications.

Nickel-chrome, precision-forged and polished blades with black tips.

Tough amber plastic handle.

Smooth Comfordome® handles fit the palm of the hand comfortably.

Chrome-plated shank helps prevent corrosion.

Internal flanges provide solid, twist-resistant shaft anchor.



7-Piece Combination Screwdriver Set

Additional Features:

- Set contains two Phillips-tip screwdrivers, two slotted keystone-tip screwdrivers and three popular cabinet-tip screwdrivers.

Cat. No.	Set Contains	Weight (lbs.)
85276		1.10

Cat. No.	Description	Shank Length
BD111	No. 1 Phillips-tip	3" (76 mm)
BD122	No. 2 Phillips-tip	4" (102 mm)
BD284	1/4" square-shank, keystone-tip	4" (102 mm)
BD306	5/16" square-shank, keystone-tip	6" (152 mm)
A216-3	1/8" round-shank, cabinet-tip	3" (76 mm)
A216-4	1/8" round-shank, cabinet-tip	4" (102 mm)
A216-6	1/8" round-shank, cabinet-tip	6" (152 mm)




85276

Pocket-Clip Screwdrivers

Additional Features:

- Round-shank screwdrivers ranging from 3-1/4" (82 mm) to 6-7/16" (164 mm) long.
- Convenient pocket clip.
- Cat. No. A010 has keystone-tip, Cat. No. P12 has Phillips-tip, and all others have cabinet-tip.



A116-4

P12

Cat. No.	Tip Size	Shank Length	Overall Length	Weight(lbs.)
Keystone-Tip and Cabinet-Tip, Pocket-Clip Screwdrivers				
A010	3/32" (2.4 mm)	1-3/8" (35 mm)	3-1/4" (82 mm)	.03
A130-2	1/8" (3.2 mm)	2" (51 mm)	3-7/8" (98 mm)	.05
A130-3	1/8" (3.2 mm)	3" (76 mm)	4-7/8" (124 mm)	.04
A116-2	3/32" (2.4 mm)	2" (51 mm)	4-7/16" (113 mm)	.05
A116-3	3/32" (2.4 mm)	3" (76 mm)	5-7/16" (138 mm)	.03
A116-4	3/32" (2.4 mm)	4" (102 mm)	6-7/16" (164 mm)	.03
A131-2	1/8" (3.2 mm)	2" (51 mm)	4-7/16" (113 mm)	.05

Cat. No.	Tip Size	Shank Length	Overall Length	Weight(lbs.)
Phillips-Tip, Pocket-Clip Round-Shank Screwdriver				
P12	No. 0	2 1/2" (63 mm)	5" (124 mm)	.05

All dimensions are in inches and (millimeters).

WARNING: Always wear approved eye protection.

WARNING: NOT insulated. Will NOT protect against electrical shock.

WARNING: Do NOT use to pry or chisel.



Plastic-Handle Screwdrivers

Midget Screwdriver

Additional Features:

- Specially designed for delicate instrument work.
- Keystone-tip screwdriver.



A000

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
A000	3/32" (2 mm)	1-1/2" (38 mm)	2-7/8" (73 mm)	.02

Keystone-Tip Screwdrivers – Square-Shanks

Additional Features:

- Oversized handle is 35% larger than comparable screwdriver handles.
- Delivers up to 50% extra power to perform tough jobs with minimum effort.



BD306

Cat. No.	Tip Size	Shank Length	Overall Length	Weight(lbs.)
BD284	1/4" (6.3 mm)	4" (102 mm)	8-1/2" (216 mm)	.25
BD286	1/4" (6.3 mm)	6" (152 mm)	10-1/2" (267 mm)	.30
BD306	5/16" (7.9 mm)	6" (152 mm)	11-3/16" (284 mm)	.35
BD308	5/16" (7.9 mm)	8" (203 mm)	13-3/16" (335 mm)	.40

Cat. No.	Tip Size	Shank Length	Overall Length	Weight(lbs.)
BD310	5/16" (7.9 mm)	10" (254 mm)	15-3/16" (385 mm)	.50
BD410	3/8" (9.5 mm)	10" (254 mm)	15-3/16" (385 mm)	.60
BD412	3/8" (9.5 mm)	12" (305 mm)	17-3/16" (437 mm)	.75
C718	3/8" (9.5 mm)	18" (457 mm)	23-5/16" (592 mm)	.95

Keystone-Tip Screwdrivers – Round-Shanks

Additional Features:

- Oversized handle is 35% larger than comparable screwdriver handles.
- Delivers up to 50% extra power to perform tough jobs with minimum effort.



BD156

Cat. No.	Tip Size	Shank Length	Overall Length	Weight(lbs.)
BD143	7/32" (5.6 mm)	3" (76 mm)	7-1/2" (190 mm)	.20
BD144	1/4" (6.3 mm)	4" (102 mm)	8-1/2" (216 mm)	.25
BD146	1/4" (6.3 mm)	6" (152 mm)	10-1/2" (267 mm)	.25
BD156	5/16" (7.9 mm)	6" (152 mm)	11-3/16" (284 mm)	.35

Cat. No.	Tip Size	Shank Length	Overall Length	Weight(lbs.)
BD158	5/16" (7.9 mm)	8" (203 mm)	13-3/16" (335 mm)	.40
BD408	3/8" (9.5 mm)	8" (203 mm)	13-3/16" (335 mm)	.50
BD510	3/8" (9.5 mm)	10" (254 mm)	15-3/16" (386 mm)	.55
70155	1/4" (6.3 mm)	20" (508 mm)	24-1/2" (622 mm)	.45

Cabinet-Tip Screwdrivers – Round-Shanks

Additional Features:

- Small-diameter shank for use in recessed holes or tight places.
- Well-suited for electrical and telecommunications work.



A216-6

Cat. No.	Tip Size	Shank Length	Overall Length	Weight(lbs.)
A230-2	1/8" (3.2 mm)	2" (51 mm)	5" (127 mm)	.05
A216-2	1/8" (3.2 mm)	2" (51 mm)	5" (127 mm)	.05
A216-3	1/8" (3.2 mm)	3" (76 mm)	6" (152 mm)	.05
A216-4	1/8" (3.2 mm)	4" (102 mm)	7" (178 mm)	.05
A216-6	1/8" (3.2 mm)	6" (152 mm)	9" (228 mm)	.05
A216-8	1/8" (3.2 mm)	8" (203 mm)	11" (279 mm)	.05

Cat. No.	Tip Size	Shank Length	Overall Length	Weight(lbs.)
A216-10	1/8" (3.2 mm)	10" (254 mm)	13" (330 mm)	.05
A316-3	3/16" (4.8 mm)	3" (76 mm)	6-5/8" (168 mm)	.10
A316-4	3/16" (4.8 mm)	4" (102 mm)	7-5/8" (194 mm)	.10
A316-6	3/16" (4.8 mm)	6" (152 mm)	9-5/8" (244 mm)	.10
A316-8	3/16" (4.8 mm)	8" (203 mm)	11-5/8" (295 mm)	.15
A316-10	3/16" (4.8 mm)	10" (254 mm)	13-5/8" (346 mm)	.20

Profiliated Phillips-Tip Screwdrivers – Round-Shanks

Additional Features:

- Oversized handle is 35% larger than comparable screwdriver handles.
- Delivers up to 50% extra power to perform tough jobs with minimum effort.



BD122

Cat. No.	Tip Size	Shank Length	Overall Length	Weight(lbs.)
BD111	No. 1	3" (76 mm)	6-5/8" (168 mm)	.10
BD122	No. 2	4" (102 mm)	8-1/2" (216 mm)	.20
BD133	No. 3	6" (152 mm)	11-3/16" (284 mm)	.35
P18	No. 1	8" (203 mm)	11-1/2" (292 mm)	.15

Cat. No.	Tip Size	Shank Length	Overall Length	Weight(lbs.)
P28	No. 2	8" (203 mm)	11-5/8" (295 mm)	.20
P212	No. 2	12" (305 mm)	15-5/8" (397 mm)	.25
P202	No. 2	20" (508 mm)	24-1/2" (622 mm)	.55

All dimensions are in inches and (millimeters).

WARNING: Always wear approved eye protection.

WARNING: NOT insulated. Will NOT protect against electrical shock.

WARNING: Do NOT use to pry or chisel.

Screwdrivers, Nut Drivers & Accessories



Specialty Plastic-Handle Screwdrivers

Magnetic Screwdriver Set

- Each screwdriver has a powerful magnet built into its shank to hold interchangeable bits and also screws.
- Comfortable handle for easier driving.
- Interchangeable bits store inside handle for quick access.
- Wide selection of bits for different screw types.



Cat. No.	Bits Included	Shank Length with Bits	Overall Length	Weight (lbs.)
70035	3/16" and 9/32" slotted and No. 1 and No. 2 Phillips	3-3/4" (95 mm)	7-1/4" (184 mm)	.25

Ratcheting Screwdriver Set

- Slotted and Phillips-tip set.
- Contains a unique 3-position ratcheting screwdriver plus an assortment of blade types and/or sizes.
- Comfortable handle with an easy-to-open snap top.
- Interchangeable bits store inside the handle for quick access.



Cat. No.	Bits Included	Shank Length with Bits	Overall Length	Weight (lbs.)
32473	3/16" and 9/32" slotted plus No. 1 and No. 2 Phillips	4-1/4" (108 mm)	8-3/4" (222 mm)	.40

Screwdriver Replacement Bits

- These precision-milled bits are 1" in length and are 1/4" hex.
- Fits replaceable-bit screwdrivers and other sockets that accept 1/4" hex bits.



Cat. No.	Bit Type	Tip Size	Weight (lbs.)
4HS316	slotted	3/16"	.02
4HS932	slotted	9/32"	.02
4H1P2	Phillips	No. 2	.02
4H1R1	square-recess	No. 1	.01
4H1R2	square-recess	No. 2	.01
4H1R3	square-recess	No. 3	.01
4HT15	TORX®	T15	.02
4HT20	TORX®	T20	.01
4HT25	TORX®	T25	.02

Cat. No.	Bit Type	Tip Size	Weight (lbs.)
4HT27	TORX®	T27	.02
4HT30	TORX®	T30	.02


Cat. No.	Weight (lbs.)
Bit Sets	Bit Selection
70036	3/16", 9/32" slotted plus No. 1 and No. 2 Phillips tips .05
70283	No. 1, No. 2, No. 3 square-recess tips .05
70432	T15, T20, T25, T27, T30 TORX® tips .05

TORX® is a registered trademark of Acument Intellectual Properties, LLC.

4-in-1 Screwdriver

- Versatile screwdriver with interchangeable, snap-in blades.
- Tool supplied with four different tips on two reversible blades.

Cat. No.	Description	Overall Length	Weight (lbs.)
32460	screwdriver with two dual-tipped blades	7-5/8" (194 mm)	.370
32478	#1 Phillips & 3/16" slotted	-	.036
32479	#2 Phillips & 9/32" slotted	-	.044



3-Piece Slotted Screw-Holding Screwdriver Set

- Not designed for torquing or tightening.

Cat. No.	Set Contains	Weight (lbs.)
SK234		.40
Cat. No.	Shank Size	
K23	3/16" x 3" (5 mm x 76 mm)	
K34	1/4" x 4" (6.3 mm x 102 mm)	
K46	5/16" x 6" (8 mm x 152 mm)	



All dimensions are in inches and (millimeters).

WARNING: NOT insulated. Will NOT protect against electrical shock.

WARNING: Always wear approved eye protection.

WARNING: Do NOT use to pry or chisel.



Specialty Plastic-Handle Screwdrivers

Slotted Screw-Holding Screwdrivers

- Split-blade screw-holding driver wedges into screw slot.
- Positive gripping action holds, starts, and drives slotted screws in awkward, hard-to-reach places.
- Not designed for torquing or tightening.

Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
K21†	1/16" (1.6 mm)	3" (76 mm)	5-1/4" (133 mm)	.05
K23	3/16" (5 mm)	3" (76 mm)	5-1/4" (133 mm)	.05
K28	3/16" (5 mm)	8" (203 mm)	10-1/4" (260 mm)	.10
K34‡	1/4" (6.3 mm)	4" (102 mm)	7-3/4" (197 mm)	.10
K36‡	1/4" (6.3 mm)	6" (152 mm)	9-3/4" (247 mm)	.15

† Precision blade for use with small precision screws. Blade thickness of .028" expanding to .045".

‡ Blade thickness of .043" expanding to .085".

Note: K21 and K23 have pocket clips.



Cat. No.	Tip Size	Shank Length	Overall Length	Weight (lbs.)
K38‡	1/4" (6.3 mm)	8" (203 mm)	11-3/4" (298 mm)	.20
K44	5/16" (8 mm)	4" (102 mm)	8-1/4" (209 mm)	.25
K46	5/16" (8 mm)	6" (152 mm)	10-1/4" (260 mm)	.25
K48	5/16" (8 mm)	8" (203 mm)	12-1/4" (311 mm)	.30

Screw-Holding Screwdrivers

Phillips-Tip Screw-Holding Screwdrivers

- Blade separates to hold the fastener.
- Not designed for torquing or tightening.
- Positive gripping action holds and starts Phillips screws in awkward, hard-to-reach places.

Cat. No.	Overall Length	Weight (lbs.)
K14	5" (127 mm) with pocket clip	.05
K16	7" (178 mm)	.05
K19	9" (229 mm)	.05




Offset Screwdrivers

Slotted-Tip Offset Screwdrivers

- Designed for confined hard-to-reach applications.
- Two tip sizes for added convenience.

Cat. No.	For Screw Nos.	Overall Length	Tip Width	Weight (lbs.)
V01	2 to 6	3" (76 mm)	3/16" (5 mm)	.01
V02	6 to 10	4-1/4" (108 mm)	1/4" (6.3 mm)	.05
V03	8 to 12	5" (127 mm)	5/16" (8 mm)	.11
V04	12 to 16	6" (152 mm)	3/8" (9.5 mm)	.25



Phillips-Tip Offset Screwdrivers

- Designed for confined hard-to-reach applications.
- Two tip sizes for added convenience.

Cat. No.	Point Nos.	Overall Length	Weight (lbs.)
P120	No. 1 and No. 2	4-3/4" (121 mm)	.05
P340	No. 3 and No. 4	6" (152 mm)	.20



Combination-Tip Offset Screwdriver

- Designed for confined hard-to-reach applications.
- Two tip sizes for added convenience.

Cat. No.	For Screw Nos.	Overall Length	Tip Width	Weight (lbs.)
V05	1/4" slotted No. 2 Phillips	5" (127 mm)	1/4" (6.3 mm)	.05



All dimensions are in inches and (millimeters).

WARNING: Always wear approved eye protection.

WARNING: NOT insulated. Will NOT protect against electrical shock.

WARNING: Do NOT use to pry or chisel.




Offset Screwdrivers

2-Piece Offset Screwdriver Set

- Designed for confined hard-to-reach applications.
- Two tip sizes for added convenience.

Cat. No.	Set Contains	Weight (lbs.)
210122	P120 (No. 1 and No. 2 Phillips-tip) and V02 (1/4" to 5/16" slotted tip)	.10




210122

Specialty Driver Set

Reversible Impact-Driver Set

- Rugged, hand-impact driver turns rusted, frozen, or other stubborn screws.
- Can also be used with 3/8" square-drive impact sockets.
- Internal, spring-loaded, helical design transforms the impact of a hammer blow to up to 200 ft.-lbs. of shock torque.
- Easily reverses for tightening or loosening screws.
- Constructed of high-grade alloy steel that has been heat-treated for added strength.
- Reclosable, seal-tight vinyl pouch with hang-up grommet.



70220

Cat. No.	Description	Weight (lbs.)
70220	pouched impact-driver set with 3/8"-square-drive fitting adapter for 5/16" hex bits, 4 assorted hex screwdriver bits (5/16" and 1/2" regular slotted tip, No. 2 and No. 4 Phillips-tip)	2.15
Replacement Screwdriver Bits		
70229	replacement set of 5/16"-drive screwdriver bits (5/16" and 1/2" regular slotted tip, No. 2 and No. 4 Phillips-tip) packed in reclosable, seal-tight vinyl pouch	.25

Torque Screwdrivers

Torque-Screwdriver Set

- Compact, easy to use set.
- Form-fitted storage box to keep set organized.

Cat. No.	Contains	Weight (lbs.)
57034	torque screwdriver Cat. No. 57035, 8-piece bit set Cat. No. 57036, rugged form-fitted storage box	1.0



57034

Torque Screwdriver

- Adjustable, torque-limiting screwdriver with calibrated micrometer scale.
- Torqued to micrometer accuracy. Accurate to $\pm 6^\circ$ plus 1/2 graduation.
- Graduated in 2 in.-lbs. (.2 NM) increments.
- Torques either clockwise or counter-clockwise.
- Can be preset and sealed for production use.
- Meets MIL-H26497 specifications.
- Easy-release bit holder. Bits are held securely during operation, yet are easily removed when released.
- Aluminum outside construction for light weight and non-magnetic characteristics.
- Non-slip grip.
- Bits not included.



57035

Cat. No.	Range	Drive Size	Overall Length	Weight (lbs.)
57035	2-36 in.-lb.	1/4" female	8" (203 mm)	.50

8-Piece Torque-Screwdriver Bits Set

- Set of eight bits for Cat. No. 57035 torque screwdriver.

Cat. No.	Contains	Weight (lbs.)
57036	Phillips No. 1 and No. 2; slotted No. 4 (3/16" x .034"), No. 5 (7/32" x .036"), No. 6 (1/4" x .038"), No. 10 (5/16" x .046"), No. 12 (3/8" x .050"); 1/4" hex-to-square male adapter	.50



57036

All dimensions are in inches and (millimeters).

WARNING: Always wear approved eye protection.

WARNING: Never use on or near live electrical circuits.

WARNING: NOT insulated. Will NOT protect against electrical shock.

WARNING: Do NOT use to pry or chisel.



Cushion-Grip Nut Driver Sets

Features:



Patented Tip-Ident®
quickly identifies nut
driver and size.

Internal flanges provide solid,
twist-resistant shaft anchor.



Full hollow shafts facilitate work
on stacked circuit boards or other
long bolt applications.

**Premium chrome-plated
shaft** for smooth feel and
corrosion resistance.

Handle end is also color
coded for easy identification.

Cushion-Grip handle
allows for greater
torque and comfort.

Meets or exceeds applicable
ASME / ANSI specifications.



7-Piece Cushion-Grip Nut Driver Set – 3" Shafts

- Set contains 630-3/16, 630-1/4, 630-5/16, 630-11/32, 630-3/8, 630-7/16, and 630-1/2. (See individual tool listings for more details.)

Cat. No.	Weight (lbs.)
631	1.50



7-Piece Hollow-Shaft* Magnetic Tip Cushion-Grip Nut Driver Set – 3" Shafts

- Full hollow shaft for long bolts or studs, with magnetic tip.
- Set contains 630-3/16M, 630-1/4M, 630-5/16M, 630-11/32M, 630-3/8M, 630-7/16M, and 630-1/2M. (See individual tool listings for more details.)

Cat. No.	Weight (lbs.)
631M	1.50

*3/16" magnetic nut driver does not have hollow shaft



631M

7-Piece Cushion-Grip Nut Driver Set – 6" Shafts

- Set contains 646-3/16, 646-1/4, 646-5/16, 646-11/32, 646-3/8, 646-7/16, and 646-1/2. (See individual tool listings for more details.)

Cat. No.	Weight (lbs.)
647	1.55



7-Piece Hollow-Shaft* Magnetic Tip Cushion-Grip Nut Driver Set – 6" Shafts

- Full hollow shaft for long bolts or studs, with magnetic tip.
- Set contains 646-3/16M, 646-1/4M, 646-5/16M, 646-11/32M, 646-3/8M, 646-7/16M, 646-1/2M. (See individual tool listings for more details.)

Cat. No.	Weight (lbs.)
647M	1.55

*3/16" magnetic nut driver does not have hollow shaft



647M

All dimensions are in inches and (millimeters).

WARNING: Always wear approved eye protection.

WARNING: NOT insulated. Will NOT protect against electrical shock.



Cushion-Grip Nut Driver Sets

4-Piece Cushion-Grip Nut Driver Set

Additional Features:

- Set contains: 630-1/4, 630-5/16, 630-3/8, 630-9/16.
(See individual tool listings for more details.)

NEW!

Cat. No.	Set Contains					Weight (lbs.)
633						1.30
Cat. No.	Color Code	Hex Size Metric	Shaft Length	Overall Length		
630-1/4	red	1/4"	3" (76 mm)	6-3/4" (171 mm)		
630-5/16	yellow	5/16"	3" (76 mm)	6-3/4" (171 mm)		
630-3/8	blue	3/8"	3" (76 mm)	6-3/4" (171 mm)		
630-9/16	orange	9/16"	4" (102 mm)	9-3/8" (238 mm)		



633

2-Piece Cushion-Grip Stubby Nut Driver Set – 1-1/2" Shafts

- Stubby nut drivers allow for work in close quarters.
- Set contains: 610-1/4, 610-5/16.
(See individual tool listings for more details.)



610

Cat. No.	Weight (lbs.)
610	.20

2-Piece Hollow-Shaft Magnetic Tip Cushion-Grip Stubby Nut Driver Set – 1-1/2" Shafts

Additional Features:

- Full hollow shaft for long bolts or studs, with magnetic tip.
- Stubby nut drivers allow for work in close quarters.
- Set contains: 610M-1/4M, 610M-5/16M.
(See individual tool listings for more details.)



Cat. No.	Weight (lbs.)
610M	.20

2-Piece Magnetic Tip Cushion-Grip Nut Driver Sets

Additional Features:

- General purpose selection of the most frequently used nut drivers.
(See individual tool listings for more details.)

Cat. No.	Set Contains	Weight (lbs.)
630M	630-1/4M, 630-5/16M	.40
646M	646-1/4M, 646-5/16M	.50



630M

7-Piece Metric Cushion-Grip Nut Driver Set – 3" Shafts

Additional Features:

- Standard length for most applications.
- Fits over long bolts and studs.

Cat. No.	Set Contains					Weight (lbs.)
65160						1.50
Cat. No.	Color Code	Hex Size Metric	Shaft Length	Overall Length		
630-5mm	black	5 mm	3" (76 mm)	6-3/4" (171 mm)		
630-5.5mm	brown	5.5 mm	3" (76 mm)	6-3/4" (171 mm)		
630-6mm	red	6 mm	3" (76 mm)	6-3/4" (171 mm)		
630-7mm	orange	7 mm	3" (76 mm)	6-3/4" (171 mm)		
630-8mm	yellow	8 mm	3" (76 mm)	6-3/4" (171 mm)		
630-9mm	green	9 mm	3" (76 mm)	6-3/4" (171 mm)		
630-10mm	blue	10 mm	3" (76 mm)	6-3/4" (171 mm)		



65160

All dimensions are in inches and (millimeters).

WARNING: Always wear approved eye protection.

WARNING: NOT insulated. Will NOT protect against electrical shock.



Cushion-Grip Stubby Nut Drivers – 1-1/2" Shafts

Additional Features:

- Full hollow shaft for long bolts or studs.
- Stubby nut drivers allow for work in close quarters.
- Meets or exceeds applicable ASME / ANSI specifications.



610-5/16

Cat. No.	Color Code	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
610-1/4	red	1/4"	1-1/2" (38 mm)	3-1/2" (89 mm)	.10
610-5/16	yellow	5/16"	1-1/2" (38 mm)	3-1/2" (89 mm)	.10

Cushion-Grip Hollow-Shaft Nut Drivers – 3" Shafts



630-1/2

Additional Features:

- Standard length for most applications.
- Fits over long bolts and studs.

Cat. No.	Color Code	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
630-3/16	black	3/16"	3" (76 mm)	6-3/4" (171 mm)	.20
630-1/4	red	1/4"	3" (76 mm)	6-3/4" (171 mm)	.20
630-5/16	yellow	5/16"	3" (76 mm)	6-3/4" (171 mm)	.20
630-11/32	green	11/32"	3" (76 mm)	6-3/4" (171 mm)	.20
630-3/8	blue	3/8"	3" (76 mm)	6-3/4" (171 mm)	.20
630-7/16	brown	7/16"	3" (76 mm)	7-5/16" (186 mm)	.25
630-1/2	red	1/2"	3" (76 mm)	7-5/16" (186 mm)	.25
630-9/16	orange	9/16"	4" (102 mm)	9-3/8" (238 mm)	.35
630-5/8	yellow	5/8"	4" (102 mm)	9-3/8" (238 mm)	.35

Refer to the insulated section for insulated nut drivers.

Metric Cushion-Grip Hollow-Shaft Nut Drivers – 3" Shafts



630-11mm

Additional Features:

- Standard length for most applications.
- Fits over long bolts and studs.

Cat. No.	Color Code	Hex Size Metric	Shaft Length	Overall Length	Weight (lbs.)
630-4mm	red	4 mm	3" (76 mm)	6-3/4" (171 mm)	.20
630-4.5mm	yellow	4.5 mm	3" (76 mm)	6-3/4" (171 mm)	.20
630-5mm	black	5 mm	3" (76 mm)	6-3/4" (171 mm)	.20
630-6mm	red	6 mm	3" (76 mm)	6-3/4" (171 mm)	.20
630-7mm	orange	7 mm	3" (76 mm)	6-3/4" (171 mm)	.20
630-8mm	yellow	8 mm	3" (76 mm)	6-3/4" (171 mm)	.20
630-10mm	blue	10 mm	3" (76 mm)	6-3/4" (171 mm)	.20
630-11mm	brown	11 mm	3" (76 mm)	7-5/16" (186 mm)	.20

Cushion-Grip Hollow-Shaft Nut Drivers – 6" Shafts

Additional Features:

- Reaches into deep recesses.
- Fits over extra-long bolts and studs.



646-1/2

Cat. No.	Color Code	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
646-3/16	black	3/16"	6" (152 mm)	9-3/4" (248 mm)	.25
646-1/4	red	1/4"	6" (152 mm)	9-3/4" (248 mm)	.25
646-5/16	yellow	5/16"	6" (152 mm)	9-3/4" (248 mm)	.25
646-11/32	green	11/32"	6" (152 mm)	9-3/4" (248 mm)	.25
646-3/8	blue	3/8"	6" (152 mm)	9-3/4" (248 mm)	.30

Cat. No.	Color Code	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
646-7/16	brown	7/16"	6" (152 mm)	10-5/16" (262 mm)	.35
646-1/2	red	1/2"	6" (152 mm)	10-5/16" (262 mm)	.35
646-9/16	orange	9/16"	6" (152 mm)	11-3/8" (289 mm)	.40
646-5/8	yellow	5/8"	6" (152 mm)	11-3/8" (289 mm)	.40

All dimensions are in inches and (millimeters).

⚠WARNING: Always wear approved eye protection.

⚠WARNING: NOT insulated. Will NOT protect against electrical shock.



Cushion-Grip Nut Drivers

Magnetic Tip Nut Drivers – Hollow Shafts*

Additional Feature:

- Exclusive hollow shaft* design with Rare Earth magnetic tip features unobstructed pass-through, even on long bolts.



630-3/8M



Cat. No.	Color Code	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
610-1/4M	1/4"	red	1-1/2" (38 mm)	1-1/2" (89 mm)	.10
610-5/16M	5/16"	yellow	1-1/2" (38 mm)	1-1/2" (89 mm)	.10
610-3/8M	3/8"	blue	1-1/2" (38 mm)	1-1/2" (89 mm)	.10
630-3/16M*	3/16"	black	3" (76 mm)	6-3/4" (171 mm)	.20
630-1/4M	1/4"	red	3" (76 mm)	6-3/4" (171 mm)	.20
630-5/16M	5/16"	yellow	3" (76 mm)	6-3/4" (171 mm)	.20
630-11/32M	11/32"	green	3" (76 mm)	6-3/4" (171 mm)	.20
630-3/8M	3/8"	blue	3" (76 mm)	6-3/4" (171 mm)	.20
630-7/16M	7/16"	brown	3" (76 mm)	7-5/16" (186 mm)	.25
630-1/2M	1/2"	red	3" (76 mm)	7-5/16" (186 mm)	.25

Cat. No.	Color Code	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
646-3/16M*	3/16"	black	6" (152 mm)	9-3/4" (248 mm)	.25
646-1/4M	1/4"	red	6" (152 mm)	9-3/4" (248 mm)	.25
646-5/16M	5/16"	yellow	6" (152 mm)	9-3/4" (248 mm)	.25
646-11/32M	11/32"	green	6" (152 mm)	9-3/4" (248 mm)	.25
646-3/8M	3/8"	blue	6" (152 mm)	9-3/4" (248 mm)	.30
646-7/16M	7/16"	brown	6" (152 mm)	10-5/16" (262 mm)	.35
646-1/2M	1/2"	red	6" (152 mm)	10-5/16" (262 mm)	.35
618-1/4M	1/4"	red	18" (457 mm)	21-3/4" (552 mm)	.50
618-5/16M	5/16"	yellow	18" (457 mm)	21-3/4" (552 mm)	.50

*3/16" magnetic nut driver does not have a hollow shaft.

Drive-A-Matic Cushion-Grip Nut Driver



632

Additional Features:

- Automatically fits 15 different nut and screw sizes.
- Hex head adjusts to the proper size as you turn it.
- Will drive or loosen hex nuts from 1/4" (6.4 mm) to 7/16" (11.1 mm), hex-head screws from No. 6 to 1/4" (6.4 mm), and socket-head cap screws from No. 8 to 5/16" (7.9 mm).

Cat. No.	Overall Length	Weight (lbs.)
632	7" (178 mm) when open, 6-3/4" (171 mm) when closed	.35

Coated Hollow-Shaft Nut Drivers



640-1/2

Additional Features:

- Entire shaft plastic coated for circuit protection only. NOT INSULATED.
- Special plastic coating resists cutting, cracking and chipping.
- Thin coating permits use in confined areas.

Cat. No.	Color Code	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
640-3/16	black	3/16"	3" (76 mm)	6-3/4" (171 mm)	.25
640-1/4	red	1/4"	3" (76 mm)	6-3/4" (171 mm)	.25
640-5/16	yellow	5/16"	3" (76 mm)	6-3/4" (171 mm)	.25
640-3/8	blue	3/8"	3" (76 mm)	6-3/4" (171 mm)	.25
640-7/16	brown	7/16"	3" (76 mm)	7-5/16" (186 mm)	.30
640-1/2	red	1/2"	3" (76 mm)	7-5/16" (186 mm)	.25
640-9/16	orange	9/16"	4" (102 mm)	9-3/8" (238 mm)	.40
640-5/8	yellow	5/8"	4" (102 mm)	9-3/8" (238 mm)	.40

⚠WARNING: NOT insulated. Coating is intended for protection of circuits only.



All dimensions are in inches and (millimeters).

⚠WARNING: Always wear approved eye protection.

⚠WARNING: NOT insulated. Will NOT protect against electrical shock.



Plastic-Handle, Hollow-Shaft Nut Driver Sets

Features:

Meets or exceeds applicable ASME / ANSI specifications.

Smooth Comfordome® handles fit the palm of the hand comfortably.

Chrome-plated shaft helps prevent corrosion.

Hollow shafts facilitate work on stacked circuit boards or other long bolt applications.

Internal flanges provide solid, twist-resistant shaft anchor.

Handles are color-coded for easy identification.




4-Piece Nut Driver Set – 3" Shafts

Additional Feature:

- *Standard length works for most applications.*

Cat. No.	Set Contains					Weight (lbs.)
70084						.60
Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length		
S8	red	1/4"	3" (76 mm)	6-5/8" (168 mm)		
S10	amber	5/16"	3" (76 mm)	6-5/8" (168 mm)		
S11	green	11/32"	3" (76 mm)	6-5/8" (168 mm)		
S12	blue	3/8"	3" (76 mm)	6-5/8" (168 mm)		



5-Piece Nut Driver Set – 3" Shafts

Additional Features:

- *Standard length works for most applications.*
- *Comes in a hang-up box.*

Cat. No.	Set Contains					Weight (lbs.)
89969						.70
Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length		
S6	black	3/16"	3" (76 mm)	6-5/8" (168 mm)		
S8	red	1/4"	3" (76 mm)	6-5/8" (168 mm)		
S10	amber	5/16"	3" (76 mm)	6-5/8" (168 mm)		
S11	green	11/32"	3" (76 mm)	6-5/8" (168 mm)		
S12	blue	3/8"	3" (76 mm)	6-5/8" (168 mm)		



All dimensions are in inches and (millimeters).

⚠WARNING: Always wear approved eye protection.

⚠WARNING: NOT insulated. Will NOT protect against electrical shock.



Plastic-Handle, Hollow Shaft Nut Driver Sets

7-Piece Nut Driver Set – 3" Shafts

Additional Feature:

- Set contains seven hollow-shaft nut drivers in the most popular hex sizes.

Cat. No.	Set Contains				Weight (lbs.)
89004					1.10
Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length	
S6	black	3/16"	3" (76 mm)	6-5/8" (168 mm)	
S8	red	1/4"	3" (76 mm)	6-5/8" (168 mm)	
S10	amber	5/16"	3" (76 mm)	6-5/8" (168 mm)	
S11	green	11/32"	3" (76 mm)	6-5/8" (168 mm)	
S12	blue	3/8"	3" (76 mm)	6-5/8" (168 mm)	
S14	brown	7/16"	3" (76 mm)	7" (178 mm)	
S16	red	1/2"	3" (76 mm)	7" (178 mm)	



89004

7-Piece Nut Driver Set – 3" Shafts

Additional Features:

- Set contains seven hollow-shaft nut drivers in the most popular hex sizes.
- Convenient vinyl pouch hangs up or rolls up.

Cat. No.	Set Contains				Weight (lbs.)
K7					1.15
Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length	
S6	black	3/16"	3" (76 mm)	6-5/8" (168 mm)	
S8	red	1/4"	3" (76 mm)	6-5/8" (168 mm)	
S10	amber	5/16"	3" (76 mm)	6-5/8" (168 mm)	
S11	green	11/32"	3" (76 mm)	6-5/8" (168 mm)	
S12	blue	3/8"	3" (76 mm)	6-5/8" (168 mm)	
S14	brown	7/16"	3" (76 mm)	7" (178 mm)	
S16	red	1/2"	3" (76 mm)	7" (178 mm)	



K7

7-Piece Nut Driver Set With Metal Stand – 3" Shafts

Additional Features:

- Set contains seven hollow-shaft nut drivers in the most popular hex sizes.
- Metal holder stands freely or hangs on wall.

Cat. No.	Set Contains				Weight (lbs.)
S700					1.60
Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length	
S6	black	3/16"	3" (76 mm)	6-5/8" (168 mm)	
S8	red	1/4"	3" (76 mm)	6-5/8" (168 mm)	
S10	amber	5/16"	3" (76 mm)	6-5/8" (168 mm)	
S11	green	11/32"	3" (76 mm)	6-5/8" (168 mm)	
S12	blue	3/8"	3" (76 mm)	6-5/8" (168 mm)	
S14	brown	7/16"	3" (76 mm)	7" (178 mm)	
S16	red	1/2"	3" (76 mm)	7" (178 mm)	



S700

All dimensions are in inches and (millimeters).

WARNING: Always wear approved eye protection.

WARNING: NOT insulated. Will NOT protect against electrical shock.



Plastic-Handle, Hollow Shaft Nut Driver Sets

10-Piece Metric Nut Driver Set With Stand – 3" Shafts

Additional Features:

- White enameled metal stand holds all ten 3"-shaft metric nut drivers.
- Identification label makes individual size selection easy.

Cat. No.	Set Contains				Weight (lbs.)
70200					1.85
Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length	
70204	black	4 mm	3" (76 mm)	6-5/8" (168 mm)	
70245	black	4.5 mm	3" (76 mm)	6-5/8" (168 mm)	
70205	black	5 mm	3" (76 mm)	6-5/8" (168 mm)	
70255	black	5.5 mm	3" (76 mm)	6-5/8" (168 mm)	
70206	black	6 mm	3" (76 mm)	6-5/8" (168 mm)	
70207	black	7 mm	3" (76 mm)	6-5/8" (168 mm)	
70208	black	8 mm	3" (76 mm)	6-5/8" (168 mm)	
70209	black	9 mm	3" (76 mm)	6-5/8" (168 mm)	
70210	black	10 mm	3" (76 mm)	7" (178 mm)	
70211	black	11 mm	3" (76 mm)	7" (178 mm)	



70200



7-Piece Nut-Driver Set – 6" Shafts

Additional Feature:

- Contains seven 6"-shaft nut drivers that reach into deep recesses.

Cat. No.	Set Contains				Weight (lbs.)
89904					1.15
Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length	
S66	black	3/16"	6" (152 mm)	9-5/8" (244 mm)	
S86	red	1/4"	6" (152 mm)	9-5/8" (244 mm)	
S106	amber	5/16"	6" (152 mm)	9-5/8" (244 mm)	
S116	green	11/32"	6" (152 mm)	9-5/8" (244 mm)	
S126	blue	3/8"	6" (152 mm)	9-5/8" (244 mm)	
S146	brown	7/16"	6" (152 mm)	10" (254 mm)	
S166	red	1/2"	6" (152 mm)	10" (254 mm)	



89904



Plastic-Handle, Hollow Shaft Nut Drivers

Stubby Nut Drivers – 1-1/2" Shafts

Additional Feature:

- Stubby nut drivers allow for work in close quarters.

Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
SS8	red	1/4"	1-1/2" (38 mm)	3-3/4" (95 mm)	.15
SS10	amber	5/16"	1-1/2" (38 mm)	3-3/4" (95 mm)	.15
SS12	blue	3/8"	1-1/2" (38 mm)	3-3/4" (95 mm)	.15



SS10



All dimensions are in inches and (millimeters).

WARNING: Always wear approved eye protection.

WARNING: NOT insulated. Will NOT protect against electrical shock.

Screwdrivers, Nut Drivers
& Accessories



Plastic-Handle Nut Drivers

Hollow-Shaft Nut Drivers – 3" & 4" Shafts



Additional Features:

- Standard length works for most applications.
- Fits over long bolts and studs.

S10

Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
S5	amber	5/32"	3" (76 mm)	6-1/2" (165 mm)	.10
S6	black	3/16"	3" (76 mm)	6-5/8" (168 mm)	.10
S7	brown	7/32"	3" (76 mm)	6-5/8" (168 mm)	.10
S8	red	1/4"	3" (76 mm)	6-5/8" (168 mm)	.15
S9	orange	9/32"	3" (76 mm)	6-5/8" (168 mm)	.15
S10	amber	5/16"	3" (76 mm)	6-5/8" (168 mm)	.15
S11	green	11/32"	3" (76 mm)	6-5/8" (168 mm)	.15
S12	blue	3/8"	3" (76 mm)	6-5/8" (168 mm)	.15
S14	brown	7/16"	3" (76 mm)	7" (178 mm)	.20
S16	red	1/2"	3" (76 mm)	7" (178 mm)	.20
S18	red	9/16"	4" (102 mm)	8-1/2" (216 mm)	.30
S20	red	5/8"	4" (102 mm)	8-1/2" (216 mm)	.30

Metric Nut Drivers – 3" Shafts



Additional Features:

- Standard length works for most applications.
- Fits over long bolts and studs.

70209

Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
70204	black	4 mm	3" (76 mm)	6-5/8" (168 mm)	.10
70245	black	4.5 mm	3" (76 mm)	6-5/8" (168 mm)	.10
70205	black	5 mm	3" (76 mm)	6-5/8" (168 mm)	.15
70255	black	5.5 mm	3" (76 mm)	6-5/8" (168 mm)	.15
70206	black	6 mm	3" (76 mm)	6-5/8" (168 mm)	.15
70207	black	7 mm	3" (76 mm)	6-5/8" (168 mm)	.15
70208	black	8 mm	3" (76 mm)	6-5/8" (168 mm)	.15
70209	black	9 mm	3" (76 mm)	6-5/8" (168 mm)	.15
70210	black	10 mm	3" (76 mm)	7" (178 mm)	.15
70211	black	11 mm	3" (76 mm)	7" (178 mm)	.20

Nut Drivers – 6" Shafts




Additional Features:

- Reaches into deep recesses.
- Fits over extra-long bolts and studs.

S86

Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
S66	black	3/16"	6" (152 mm)	9-5/8" (244 mm)	.15
S86	red	1/4"	6" (152 mm)	9-5/8" (244 mm)	.15
S106	amber	5/16"	6" (152 mm)	9-5/8" (244 mm)	.15
S116	green	11/32"	6" (152 mm)	9-5/8" (244 mm)	.15
S126	blue	3/8"	6" (152 mm)	9-5/8" (244 mm)	.15
S146	brown	7/16"	6" (152 mm)	10" (254 mm)	.20

Magnetic Nut Drivers – Solid Shafts



Additional Feature:

- Powerful nut-holding magnet built into solid shaft.

S106M

Cat. No.	Handle Color	Hex Size	Shaft Length	Overall Length	Weight (lbs.)
S8M	red	1/4"	3" (76 mm)	6-5/8" (168 mm)	.15
S10M	amber	5/16"	3" (76 mm)	6-5/8" (168 mm)	.15
S86M	red	1/4"	6" (152 mm)	9-5/8" (244 mm)	.15
S106M	amber	5/16"	6" (152 mm)	9-5/8" (244 mm)	.15
S126M	blue	3/8"	6" (152 mm)	9-5/8" (244 mm)	.15
S818M	red	1/4"	18" (457 mm)	21-5/8" (549 mm)	.25
S1018M	amber	5/16"	18" (457 mm)	21-5/8" (549 mm)	.25

Super-Long Nut Drivers – 18" Shafts



Additional Features:

- Heavy-duty, long-reach nut drivers.
- Ideal for reaching into walls and other hard-to-reach places where added length is necessary.
- Available in magnetic and non-magnetic tip.

S1018

Cat. No.	Handle Color	Hex Size	Shaft Length	Type	Overall Length	Weight (lbs.)
S818	red	1/4" (6.3 mm)	18" (457 mm)	standard	21-5/8" (549 mm)	.25
S818M	red	1/4" (6.3 mm)	18" (457 mm)	magnetic	21-5/8" (549 mm)	.25
S1018	amber	5/16" (7.9 mm)	18" (457 mm)	standard	21-5/8" (549 mm)	.25
S1018M	amber	5/16" (7.9 mm)	18" (457 mm)	magnetic	21-5/8" (549 mm)	.25

All dimensions are in inches and (millimeters).

WARNING: Always wear approved eye protection.

WARNING: NOT insulated. Will NOT protect against electrical shock.



Cushion-Grip Triple Taps and Six-in-One Tap Tool

- Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions.
- Each tap size rethreads to next larger size if threads are stripped.

Cat. No.	Tap Sizes	Overall Length	Weight (lbs.)
623-20	Triple Tap 10-24, 12-24, 1/4-20	7-3/4"	.25
623-24	Triple Tap 6-32, 8-32, 10-24	7-3/4"	.25
623-32	Triple Tap 6-32, 8-32, 10-32	7-3/4"	.25
626	6-in-1 Tap 6-32, 8-32, 10-32, 10-24, 12-24, 1/4-20	7-3/4"	.25



626

Replacement Taps

628-20	10-24, 12-24, 1/4-20	replacement for 623-20, 626
626-24	6-32, 8-32, 10-24	replacement for 623-24
626-32	6-32, 8-32, 10-32	replacement for 623-32, 626

Six-in-One Tapping Tool



627-20

- Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions.
- Each tap size rethreads to next larger size if threads are stripped.
- Two high-carbon steel taps are secured in reversible holder.

Cat. No.	Tap Sizes	Overall Length	Weight (lbs.)
627-20	6-32, 8-32, 10-32, 10-24, 12-24, 1/4-20	7-5/8" (194 mm)	0.35

Replacement Taps

626-32	10-32, 8-32, 6-32
628-20	10-24, 12-24, 1/4-20

Triple Taps



625-24

- Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions.
- Each tap size rethreads to next larger size if threads are stripped.

Cat. No.	Tap Sizes	Color Code	Overall Length	Weight (lbs.)
625-24	6-32, 8-32, 10-24	blue	7-1/8" (181 mm)	0.20
625-32	6-32, 8-32, 10-32	orange	7-1/8" (181 mm)	0.20

Replacement Taps

626-24	for Cat. No. 625-24
626-32	for Cat. No. 625-32

Cushion-Grip Scratch Awl



650

- Professional, heavy-duty, hard-pointed awl.
- Scribes metal, starts screw holes, performs a variety of piercing and punching jobs.
- Rigid, chrome-plated, heat-treated, tempered-steel shank has full reinforcing bolster at handle for extra strength and for handle impact reinforcement.
- Internal flanges provide solid shank anchor.
- Cushion-Grip handle allows for greater comfort.

Cat. No.	Blade Length	Overall Length	Weight (lbs.)
650	3-1/2" (89 mm)	7-7/8" (200 mm)	.25

WARNING: Do NOT hammer on tool.

Steel Scratch Awl



66385

- One-piece forged-steel blade and bolstered shank.
- Heat treated for long life.
- Well-balanced for top efficiency during use.
- Black finish for rust resistance.

Cat. No.	Blade Length	Overall Length	Weight (lbs.)
66385	3-1/2" (89 mm)	7" (178 mm)	.30

WARNING: NOT insulated. Will NOT protect against electrical shock.

WARNING: Never use on or near live electrical circuits.

All dimensions are in inches and (millimeters).

WARNING: Always wear approved eye protection.



Spring Tools

Cushion-Grip Spring Tool



ST4

- Installs or removes small-diameter coil springs on motors, brake shoes, headlights, relays, installing recessed can lighting, solenoids, and hundreds of other applications.
- Great for rod and leaf springs.
- Unique C-tip prevents spring slippage.
- Cushion-Grip handle for greater comfort.

Cat. No.	Shank Length	Overall Length	Weight (lbs.)
ST4	4" (102 mm)	7-3/4" (197mm)	.17
ST6	6" (152 mm)	9-3/4" (248 mm)	.19

Spring Tool



ST49

- Installs or removes small-diameter coil springs on motors, brake shoes, headlights, relays, can lighting, solenoids, and hundreds of other applications.
- Great for rod and leaf springs.
- Unique C-tip prevents spring slippage.

Cat. No.	Overall Length	Weight (lbs.)
ST49	7-1/2" (191 mm)	.10

Spring Tool Set

2-Piece Recessed Can Light Tool Set

- Contains the two tools needed for finishing can light installations in record time.
- Long reach, spring tool (Cat. No. ST6) makes attaching difficult springs easy.
- Compact, stubby nut driver (Cat. No. 610-1/4) even fits in smaller cans to tighten hard to reach ceiling height adjustment screws.
- Cushion-Grip handles for greater torque and comfort.



65020

Cat. No.	Set Contains	Weight (lbs.)
65020		.36

Cat. No.	Description	Shank Length	Overall Length
ST6	6" spring tool	6" (152 mm)	9-3/4" (248 mm)
610-1/4	1/4" stubby nut driver	1-1/2" (38 mm)	3-1/2" (89 mm)

All dimensions are in inches and (millimeters).

WARNING: Always wear approved eye protection.

WARNING: NOT insulated. Will NOT protect against electrical shock.

