

Flat zack marker sheet - ZBFM 5:SO/CMS - 0803647

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Flat zack marker sheet, white, For terminal block width: 5.2 mm

The illustration shows the versions ZBM and ZBFM

Key commercial data

Packing unit	1
Minimum order quantity	1
Catalog page	Page 403 (CL-2005)
GTIN	 4 017918 007607
Weight per Piece (excluding packing)	4.8 GRM
Country of origin	GERMANY

Technical data

General

Note	Please specify the required marking and color with order.
Color	white
Inflammability class according to UL 94	V2
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 100 °C
Components	free from silicone and halogen
Pitch	5.2 mm
Material	PA
Number of individual labels	120
Pitch	5.2 mm

Classifications

eclass

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27149103

Flat zack marker sheet - ZBFM 5:SO/CMS - 0803647

Classifications

eclass

eCl@ss 6.0	27149103
------------	----------

etim

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761

unspsc

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Marking

Marker pen - B-STIFT - 1051993



Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm

Marker pen - X-PEN 0,35 - 0811228



Marker pen without ink cartridge, for manual labeling of markers, labeling extremely wipe-proof, line thickness 0.35 mm