



GK20M

Flue temperature probe



Copyright © 2007 Test Products International, Inc.

Application

Exposed junction with cone stop,
fast response in flue temperature
applications

Range°F°C

-40° to 932°F
-40° to 260°C

Probe tip

42

Dimensions

Stem Length: 4.33" (1120m)
Diameter: 0.24" (6mm)
Lead Length: 16" (4.9M)

Insulation Material

Teflon