

# Superflex® Speaker Wire

UL Listed

## Product Construction:

### Conductor:

- 12 AWG fully annealed stranded bare copper conductor per ASTM B-3

### Insulation/Jacket:

- Premium-grade, clear Superflex® PVC
- Temperature range: -20°C to +60°C
- Color code: See chart below

## Applications:


- Digital audio
- Hi-fi and stereo speaker wire
- Jukeboxes
- Not for in-wall use

## Compliances:

- UL Misc. (UL: 120V)
- RoHS Compliant Directive 2002/95/EC

## Packaging:

- Please contact Customer Service for packaging and color options



| CATALOG NUMBER | NUMBER OF COND. | AWG SIZE | COND. STRAND | NOM. INSULATION THICKNESS |      | NOMINAL O.D. |            |
|----------------|-----------------|----------|--------------|---------------------------|------|--------------|------------|
|                |                 |          |              | INCHES                    | mm   | INCHES       | mm         |
| <b>C1364</b>   | 2               | 12       | 7x37/36      | 0.060                     | 1.52 | 0.220x0.456  | 5.59x11.58 |

### Color Code Chart

| ORDERING SUFFIX | STOCK COLOR |
|-----------------|-------------|
| <b>90</b>       | Clear       |

## Product Construction:

### Conductor:

- 18 AWG, 1 tinned and 1 bare copper conductor per ASTM B-174

### Insulation:

- Premium-grade, clear PVC

### Jacket:

- PVC, clear
- Temperature range: -20°C to +60°C

## Applications:


- Digital audio
- Hi-fi and stereo speaker wire
- Jukeboxes

## Compliances:

- RoHS Compliant Directive 2002/95/EC

## Packaging:

- Please contact Customer Service for packaging and color options




| CATALOG NUMBER | NO. OF COND. | AWG SIZE | COND. STRAND | NOM. INSULATION THICKNESS |      | NOM. JACKET THICKNESS |      | NOMINAL O.D. |      |
|----------------|--------------|----------|--------------|---------------------------|------|-----------------------|------|--------------|------|
|                |              |          |              | INCHES                    | mm   | INCHES                | mm   | INCHES       | mm   |
| <b>C6367</b>   | 2            | 18       | 16/30        | 0.016                     | 0.41 | 0.025                 | 0.64 | 0.210        | 5.33 |


### Color Code Chart

| ORDERING SUFFIX | STOCK COLOR |
|-----------------|-------------|
| <b>90</b>       | Clear       |

# Pro Audio Speaker Wire



| CATALOG NUMBER | CONDUCTOR & O.D.                      | INSULATION & O.D. | JACKET & O.D.   | WEIGHT LBS/Mft |
|----------------|---------------------------------------|-------------------|-----------------|----------------|
| 740002         | 2/C 12 AWG Stranded 65/30 Bare Copper | PVC 0.136" Nom.   | PVC 0.365" Nom. | 100            |
| 740102         | 2/C 14 AWG Stranded 41/30 Bare Copper | PVC 0.118" Nom.   | PVC 0.295" Nom. | 75             |
| 740202         | 2/C 16 AWG Stranded 26/30 Bare Copper | PVC 0.102" Nom.   | PVC 0.295" Nom. | 60             |
| 740302         | 2/C 18 AWG Stranded 41/34 Bare Copper | PVC 0.079" Nom.   | PVC 0.235" Nom. | 38             |



| CATALOG NUMBER | CONDUCTOR & O.D.                      | INSULATION & O.D. | JACKET & O.D.   | WEIGHT LBS/Mft |
|----------------|---------------------------------------|-------------------|-----------------|----------------|
| 740004         | 4/C 12 AWG Stranded 65/30 Bare Copper | PVC 0.136" Nom.   | PVC 0.463" Nom. | 165            |
| 740104         | 4/C 14 AWG Stranded 41/30 Bare Copper | PVC 0.118" Nom.   | PVC 0.397" Nom. | 107            |
| 740204         | 4/C 16 AWG Stranded 26/30 Bare Copper | PVC 0.102" Nom.   | PVC 0.338" Nom. | 75             |
| 740304         | 4/C 18 AWG Stranded 41/34 Bare Copper | PVC 0.079" Nom.   | PVC 0.283" Nom. | 53             |

NOTE: Cabled with jute fillers and paper tape under jacket.

## Product Construction:

### Conductor:

- 12-18 AWG stranded bare copper
- Twisted pairs

### Insulation:

- PVC

### Jacket:

- PVC, matte black
- High flexibility

### Applications:

- Recording studios
- Commercial broadcast facilities
- Not for in-wall use

### Features:

- High durability and long-lasting service

### Packaging and Jacket Colors:

- Please consult Customer Service for packaging, color options and agency approvals

## Color Code Chart

| NO. OF COND. | COLOR |
|--------------|-------|
| 1            | Black |
| 2            | White |
| 3            | Red   |
| 4            | Green |