


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



SEE SHEET 2 FOR SPECIFICATIONS

[illegible]

NOTES UNLESS OTHERWISE SPECIFIED:

PANDUIT TOOL NUMBER CT-980 DIELESS CRIMP TOOL INSTALLS # 4 AWG THRU 750 MCM COPPER CONNECTORS AND # 6 AWG THRU 500 MCM ALUMINUM CONNECTORS.

TOOL OUTPUT = 5.5 METRIC TONS / 6.2 SHORT TONS

TOOL WEIGHT = 11.4 LBS / 5.2 Kg

TOOL HAS YELLOW FIBERGLASS HANDLES WITH BLACK RUBBER GRIPS

HINGED TOOL HEAD ROTATES FREELY (180 DEGREES) AND LOCKS IN PLACE WITH PIN AND D-RING

TOOL CRIMP HEAD ROTATES 360 DEGREES ABOUT LOWER HANDLE CENTER LINE

DO NOT USE TOOL ON LIVE CIRCUITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

1.X1 ±	1.XXX ±
1.XX ±	ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY	MAT'L
----------	-------

SCALE	
-------	--

DATE	
------	--

SHEET 2 OF 2

TP24501A01

DOT
A

00 SEE SHEET 1 FOR RELATED INFO

3985

RFL

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP
-----	------	----	-----	-------------	---------	------	-----