



## MATERIALS:

Conn. 1<sup>st</sup> End – Triaxial Cable Plug

Body and Fittings: Brass, Tarnish resistant plating

Intermediate and Center contacts: Gold Plated Brass

Cable: Belden 9272. Nominal Impedance: 78 Ohms. 2 conductor shielded, 20 AWG stranding 7 x 28 tinned copper.

Insulation: Polyethylene. Color: Blue

Conn. 2<sup>nd</sup> End - Triaxial Cable Plug

Body and Fittings: Brass, Tarnish resistant plating

Intermediate and Center Contacts: Gold Plated Brass

## RATINGS:

Operating Temperature: +80°C. (+176°F.)

Operating Voltage: 500 VRMS

## ORDERING INFORMATION: Model 3581-CC-XX

XX=Length in inches. Std. Lengths: 18" (45,72 cm), 24" (60,96 cm), 36" (91,44 cm), 48" (121,92 cm) & 60" (152,40 cm). Additional lengths can be quoted upon request.

Ordering Example: 3581-CC-36, Cable length will be 36" (9,44 mm) long.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[3581-CC-18](#) [3581-CC-36](#) [3581-CC-24](#) [3581-CC-60](#) [3581-CC-48](#)