


DC Power Jack 1.3mm

163-2230-E

KOBICONN

DC Power Jack 1.3mm



Dimensions: mm

ELECTRICAL SPECIFICATIONS

1	Current rating: 3.0A max.
2	Voltage rating: 24V max.
3	Contact resistance: 100mΩ min.
4	Insulation resistance: 100mΩ min.
5	Withstanding voltage: 25V AC for 1 minute.
RoHS Compliant	

MATERIAL SPECIFICATIONS

ITEM	SPECIFICATIONS
1	Housing: High temp. plastic
2	Terminal: Copper Alloy
3	Plating: Silver over Nickel
RoHS Compliant	

Date Last Revised: 06/29/12

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301317

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

163-2230-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[163-2230-E](#)