


| PANDUIT<br>PART NUMBER | STUD<br>SIZE | DIMENSIONS in. |                |               |                |               |
|------------------------|--------------|----------------|----------------|---------------|----------------|---------------|
|                        |              | A $\pm .03$    | W $\pm .01$    | C MIN         | M $\pm .03$    | H $\pm .01$   |
| P18-6F                 | #6           | .63<br>(16.00) | .30<br>(7.62)  | .21<br>(5.33) | .49<br>(12.45) | .15<br>(3.81) |
| P18-6FN *              | #6           | .63<br>(16.00) | .24<br>(6.10)  | .19<br>(4.83) | .49<br>(12.45) | .15<br>(3.81) |
| P18-8F                 | #8           | .69<br>(17.53) | .32<br>(8.13)  | .25<br>(6.35) | .53<br>(13.46) | .17<br>(4.32) |
| P18-10F                | #10          | .71<br>(18.03) | .35<br>(8.89)  | .25<br>(6.35) | .55<br>(13.97) | .20<br>(5.08) |
| P18-10FN *             | #10          | .71<br>(18.03) | .31<br>(7.87)  | .25<br>(6.35) | .55<br>(13.97) | .20<br>(5.08) |
| P18-14F                | 1/4"         | .88<br>(22.35) | .44<br>(11.18) | .33<br>(8.38) | .63<br>(16.00) | .27<br>(6.86) |

## NOTES:

- UL LISTED AND CSA CERTIFIED FOR:  
A. #22-16 AWG SOLID OR STRANDED  
COPPER WIRE
- MATERIAL:  
A. STAMPING - .03" (.76) THK COPPER,  
TIN PLATED
- 302°F (150°C) MAX USE TEMP
- SEE [www.panduit.com](http://www.panduit.com) FOR PART NUMBER SUFFIX  
DESIGNATION FOR PACKAGE SIZE.
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
- INSTALLATION TOOLS:  
A. UL LISTED AND CSA CERTIFIED: CT-100  
CT-100A, CT-200, CT-570, CT-600-A,  
CT-1570, CT-2500  
B. PANDUIT APPROVED: CT-160, CT-260
- WIRE STRIP LENGTH: 9/32  $^{+1/32}_{-0}$  (7.1  $^{+.8}_{-0}$ )
- (\*) THESE PARTS NOT UL LISTED OR CSA CERTIFIED



LISTED  
587H  
E52164



CERTIFIED  
LR31212

|     |      |      |                                                                         |     |     |                                                                                          |       |       |             |
|-----|------|------|-------------------------------------------------------------------------|-----|-----|------------------------------------------------------------------------------------------|-------|-------|-------------|
| 06  | 5/11 | SHOR | MODIFIED NOTE #4,<br>ADDED INSTALLATION TOOLS                           |     |     | <div><div><div>PANDUIT</div><div>CORP.</div></div><div>TINLEY PARK, ILLINOIS</div></div> |       |       |             |
| 05  |      | JKD  | ADDED CT-1570 TOOL                                                      |     |     |                                                                                          |       |       |             |
| 04  | 1/97 | TM   | ADDED NARROW TONGUE FORKS AND 1/4" STUD<br>FILESPEC WAS N41461AA_PCD_03 | LCA | KRS | #22-18 BARREL NON-INSULATED FORK                                                         |       |       |             |
| 03  | 7/95 | MC   | UPDATED NOTES AND DIMENSIONS                                            | TJP | KRS |                                                                                          |       |       |             |
| REV | DATE | BY   | DESCRIPTION                                                             | APP | PM  | DRAWN BY                                                                                 | CHK'D | SCALE | DRAWING NO. |
|     |      |      |                                                                         |     |     | DRL                                                                                      |       | NONE  | A41461      |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[P18-8F-M](#) [P18-10FN-C](#) [P18-6FN-M](#) [P18-10F-C](#) [P18-14F-C](#) [P18-6F-C](#) [P18-8F-C](#) [P18-10FN-CY](#) [P18-6R-MY](#) [P18-14F-MY](#) [P18-P47-CY](#) [P18-10RHT6-MY](#) [P18-10F-MY](#) [P18-10F-M](#) [P18-6F-M](#) [P18-14F-M](#) [P18-6FN-C](#)