


Chrome Panel Mount

- **Nickle Plated Brass Housings**
- **Enhanced Viewing Angles**
- **Daylight Visible Available**
- **Rugged Design**
- **Additional Specifications, See Pages 38-39**




MPC3 SERIES

Chrome Panel Mount




MPC5 SERIES

Chrome Panel Mount




MPR3 SERIES

Chrome Panel Mount



MPR5 SERIES

Chrome Panel Mount



PART NO.	CHIP		LENS APPEARANCE	ELECTRO-OPTICAL DATA IF=20mA			VIEWING ANGLE (deg)
	EMITTED COLOR	PEAK (nm)		Vf(V) Type	Max	iV Typ. (mcd)	
MPX3GD	GREEN	565	GREEN DIFFUSED	2.2	2.6	40.0	40
MPX3HD	HE RED	635	RED DIFFUSED	2.0	2.6	40.0	40
MPX3YD	YELLOW	585	YELLOW DIFFUSED	2.1	2.6	30.0	40
MPX3SRD	SUPER RED	660	RED DIFFUSED	1.7	2.6	120.0	50
MPX3BWD	BLUE	430	BLUE DIFFUSED	5.0	5.5	15.0	45
MPX5GD	GREEN	565	GREEN DIFFUSED	2.2	2.6	50.0	55
MPX5HD	HE RED	635	RED DIFFUSED	2.0	2.6	50.0	55
MPX5YD	YELLOW	585	YELLOW DIFFUSED	2.1	2.6	40.0	55
MPX5SR	SUPER RED	660	RED DIFFUSED	1.7	2.6	150.0	50
MPX5BWD	BLUE	430	BLUE DIFFUSED	5.0	5.5	15.0	45

X=Housing Style "R" or "C"

ORDERING INFORMATION EXAMPLE:

MPR 5 G D X X
 | | | |
 SERIES LED SIZE COLOR LENS OPTIONS