


D

C

B

A



1 STAMP AMP 2W* 60-75 APPROX AS SHOWN

321201
AMP
PART NUMBER

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN DK SCHRUM 020CT97		AMP Incorporated Harrisburg, PA 17105-3608						
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±0.20 [0.008] 3 PLC ±- 4 PLC ±- ANGLES ±-	CHK MJ SPICER 030CT97	AMP	NAME TERMINAL, RING TONGUE, FLAG, SOLISTRAND™					
		VOLTAGE RATING: NOT APPLICABLE	MATERIAL COPPER PER ASTM B-152 ANNEALED			FINISH TIN PLATE 0.00254 [0.000100] MIN THK PER ASTM B-545					APVD JL MECKLEY 030CT97		
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 26.7-42.4mm² [52,600-83,700] CIR MILS SOLID OR STRANDED	PRODUCT SPEC -		APPLICATION SPEC -	WEIGHT -					SIZE A3	CAGE CODE 00779	DRAWING NO C-321201
FOR ORDER ENTRY	1-800-526-5142	CUSTOMER DRAWING									SCALE 2:1	SHEET 1 OF 1	REV C