



Sample photo

**Order symbol:** PCM 125/60 G  
**Product nbr:** 6016307  
**Description:** Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074038036  
**El. number:**  
Finland: 3421635  
Denmark: 8212027064  
Italy: 7341025  
Sweden: 2535312  
Norway: 2535509

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

| Dimensions:            |  | Length                            | Width | Height | Rating:                                      |
|------------------------|--|-----------------------------------|-------|--------|----------------------------------------------|
| mm:                    |  | 130                               | 130   | 60     | Ingress Protection (EN 60529): IP 66/67      |
| inch:                  |  | 5.1                               | 5.1   | 2.4    | Impact Resistance (EN 62262): IK 08          |
| Materials:             |  |                                   |       |        | Electrical insulation: Totally insulated     |
| Material:              |  | Polycarbonate                     |       |        | Halogen free (DIN/VDE 0472, Part 815): Yes   |
| Base colour:           |  | RAL 7035                          |       |        | UV resistance: UL 508                        |
| Cover colour:          |  | RAL 7035                          |       |        | Flammability Rating (UL 746 C 5): UL 746C 5V |
| Cover screws material: |  | Polyamide                         |       |        | Glow Wire Test (IEC 695-2-1) °C: 960         |
| Cover screws colour:   |  | Grey                              |       |        | NEMA Class: NEMA 1, 4, 4X, 6                 |
| Gasket material:       |  | TPE                               |       |        | Certificates:                                |
| Temperatures:          |  |                                   |       |        | Germanischer Lloyd (GL)                      |
| Short term:            |  | -40 ... 120 °C                    |       |        | Underwriters Laboratories                    |
| Continuous:            |  | -40 ... 80 °C                     |       |        | Det Norske Veritas                           |
| Short term:            |  | -40 ... 250 °F                    |       |        | Fimko                                        |
| Continuous:            |  | -40 ... 175 °F                    |       |        | Europe EN 62208: 2003                        |
| Accessories:           |  |                                   |       |        | UL Canada                                    |
| MIV 125                |  | Mounting plate (Galvanized steel) |       |        | Gost R                                       |
| MIN 10                 |  | DIN-15 Mounting rail              |       |        |                                              |
| MIV 10                 |  | DIN-35 Mounting rail              |       |        |                                              |
| FP A 125/130           |  | Front plate (Aluminium)           |       |        |                                              |
| HFP 130                |  | Front plate hinge series          |       |        |                                              |
| FP 22046               |  | Wall fastening lug (4 pcs)        |       |        |                                              |

