


RNF100



## Dimensions (in millimetres)


| Part Number | Inside Diameter                    |                                       | Wall Thickness                        |
|-------------|------------------------------------|---------------------------------------|---------------------------------------|
|             | D (min)<br>Expanded<br>as supplied | d (max)<br>Recovered<br>after heating | W (nom)<br>Recovered<br>after heating |

|               |     |     |     |
|---------------|-----|-----|-----|
| RNF100 NR.541 | 6.0 | 1.6 | 0.5 |
|---------------|-----|-----|-----|

|               |     |     |     |
|---------------|-----|-----|-----|
| RNF100 NR.610 | 5.3 | 1.6 | 0.5 |
|---------------|-----|-----|-----|

RNF 100 NR. 541 Available in colours only (not clear)

RNF 100 NR. 610 Available in colours and clear.

Issued by  Issue 2

Date 7 March 1978

Approved by

