






LOC		DIST		REVISIONS					
FT		0		P	LTR	DESCRIPTION	DATE	DWN	APVD
				P		ADDED 1-2, 1-3 ECO-06-002610	15FEB2006	SW	SH
				P	I	REVISED PER ECO-09-025699	12DEC2009	KK	AEG




- HOUSING: NYLON, UL 94 V-0 RATED, BLACK.
- CONTACT:
BODY - BRASS, .000100 MIN TIN-LEAD OVER .000050 MIN NICKEL.
POST - BRASS, .000100 MIN TIN-LEAD OVER .000050 MIN NICKEL.
- CONTACT:
BODY - BRASS, .000100 MIN TIN OVER .000050 MIN NICKEL.
POST - BRASS, .000100 MIN TIN OVER .000050 MIN NICKEL.
- PERIPHERAL SEAL: ELASTOMER, GRAY.
- KEYING PLUG: NYLON, NATURAL.
- .009 MAXIMUM CONTACT LEAD-IN SEAM GAP PERMISSIBLE
ON MATING FACE END.
- OBsolete PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



DETAIL V
SCALE 20:1



RECOMMENDED PC BOARD LAYOUT
SCALE 3:1



RECOMMENDED PANEL LAYOUT
.125 MAX PANEL THICKNESS
SCALE 3:1

7	POSN 9	YES	3	8	1-8	1-213826-3
7	-	YES	3	8	1-5,7-9	1-213826-2
	-	YES	3	9	ALL	1-213826-1
7	POSN 9	YES	3	8	1-8	1-213826-0
7	-	YES	3	8	1-5,7-9	213826-9
	POSN 9	YES	2	8	1-8	213826-8
	-	YES	2	8	1-5,7-9	213826-7
7	POSN 9	YES	2	8	1-8	213826-3
7	-	YES	2	8	1-5,7-9	213826-2
	-	YES	2	9	ALL	213826-1
KEYING PLUG		PERIPHERAL SEAL	FINISH	QTY	SELECT LOAD IN POSITIONS	PART NUMBER
			CONTACTS			

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

©

COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION, ALL RIGHTS RESERVED.

9 PLC ±.0

2 PLC ±0.00

3 PLC ±0.010

4 PLC ±0.0000

ANGLES ±.

FINISH

TYCO ELECTRONICS CORPORATION

TYCO ELECTRONICS CORPORATION

TYCO ELECTRONICS CORPORATION

LOC

DIST

FT

23MAY2003

23MAY2003

23MAY2003

NAME

RECEPTACLE ASSEMBLY, POSTED, REVERSE SEX, SERIES 1, 17-9, CPC

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

SCALE

4:1

SHEET

1

OF

1

REV

P

CUSTOMER DRAWING