

Ratings:

Current 10A
Voltage 300 V
Wire Size 30-16AWG
Test Voltage 1.25 kV
Rated Torque / Screw Size 0.4Nm / M2

Rated Cross Section:


Single Wire (solid) 1.5mm²
Stranded Wire (flexible) 1.0mm²
Stranded Wire with Ferrules 0.5mm²

Dimensions:

Spacing 3.81mm
PCB Hole Diameter 1.1mm
Stripped Length 5.0mm

Materials:

Insulating Material PA
Flammability UL94V-0
Temperature -30°C/+105°C
Block CuZn
Wire Guard Cu
Color Green



ON - SHORE TECHNOLOGY, INC.

Part Number

EDZ602/[*][*]

* - NUMBER OF POSITIONS

Units

mm

Drawing

Reviewed

Approved

Date

1/16/99

Sheet 1 of 1