


DL-806 Series The Professional Hex Crimping Tool For Crimping BNC,F,TNC Connectors.

Specification:

Item No:



w/ Adjustment

DL-	 ± 0.10			Crimping Cable Size
806A	.255"(6.48mm)	.213"(5.40mm)	.068"(1.72mm)	RG-58,59,62
806B	.324"(8.22mm)	.255"(6.48mm)	.068"(1.72mm)	RG-59,62,6
806C	.324"(8.22mm)	.216"(5.48mm)	.068"(1.72mm)	RG-58,6
806D	.255"(6.48mm)	.213"(5.40mm)	.068"(1.72mm)	RG-58,59,62
806E	.213"(5.40mm)	.324"(8.22mm)	.448"(11.4mm)	RG-58,6,11,213
806F	.100"(2.54mm)	.324"(8.22mm)	.476"(12.1mm)	RG-6,11,213
806G	.100"(2.54mm)	.324"(8.22mm)	.448"(11.4mm)	RG-6,11,213 BELDEN8281
806H	.324"(8.22mm)	.359"(9.12mm)		F-59,62,6
806J	.472"(12.1mm)	.361"(9.18mm)		F-59,6,11
806L	.100"(2.54mm)	.359"(9.12mm)	.406"(10.3mm)	F-59,6,11& UHF-58,8
806M	.100"(2.54mm)	.359"(9.12mm)	.475"(12.06mm)	F-59,6,11
806N	.133"(3.38mm)	.151"(3.84mm)	.122"(3.10mm)	.188"(4.78mm) ST/SC FIBER OPTIC
806P	.095"(2.41mm)	.386"(9.80mm)	.453"(11.5mm)	
806Q	.324"(8.22mm)	.470"(11.94mm)		F-59,6,11,213
806R	.480"(12.19mm)	.362"(9.19mm)		F-59,6,11
806S	.102"(2.60mm)	.406"(10.30mm)		UHF-8
806T	.096"(2.44mm)	.410"(10.40mm)	.475"(12.06mm)	UHF-8,F-11
806U	.255"(6.48mm)	.068"(1.72mm)	.360"(9.14mm)	F-59,6
806X	.076"(1.93mm)	.338"(8.60mm)		TWINAX CONN

*All Above Tools With Adjustment, Except DL-806A

* **Length:** 9" (225+/-3mm)

* **Material:** Carbon Steel And Hardness

* **Weight:** 380g

* **Finished:** Black oxide finished.

01/30/03
REV.1