

9330N/ND Mono Laser Printer

Transform Your Business



- Up to 30 ppm letter 28 ppm A4
- Choice of models Simplex or Duplex
- Small and compact design
- 1200 x 1200 dpi print quality
- 8.5 Seconds first time to print
- Ideal for workgroups or small networks

Small and Efficient

Ideally suitable for workgroups or small networks, the feature rich 9330 mono laser printer will transform your documents increasing overall efficiency in your office. True 1200 dpi print quality coupled with a very respectable 28 page per minute A4 will ensure the 9330 range delivers professional quality output all within your budget.

Choice of Models

The **9330N** offers two input paths, a 250 sheet cassette together with a 50 sheet multi-purpose feeder ideal for those non standard paper sizes. PCL and PostScript 3 is standard together with 64 Mb of onboard memory expandable to 320 Mb, will ensure the 9330N will speed through the most complex applications.

For duplex printing, the **9330ND** comes complete with its own built-in duplexer for hassle-free double sided printing on a wide variety of paper types and sizes. Both models can benefit from an additional optional 250 sheet cassette which can be simply installed by the user.

Versatile

USB 2.0 connectivity is standard on all models for high use personal users together with Ethernet 10/100BaseT and parallel, making the 9330 the most versatile printers available today. PCL and PostScript together with a range of Windows driver setup utilities will ensure the 9330 will connect to virtually anything.

Available Configuration:

9330N - Simplex model
9330ND - Duplex model

Print Speed	Simplex (9330N):Up to 30 pages per minute letter, 28 pages per minute A4. Duplex (9330ND):Up to 21 pages per minute letter, up to 19 pages per minute A4
Print Method	Laser
Processor	SPGPv3 processor at 400 MHz
Resolution	1200 x 1200 dpi
Time To 1st Page	First Page: Less than 8.5 seconds
Memory	64MB Standard, 320MB Maximum
Standard Connectivity	Parallel (Bi-directional IEEE 1284 compliant ECP/Nibble/Byte Mode), USB (v 2.0), Internal Ethernet (10BaseT & 100BaseTx); Automatic Interface Switching
Standard Emulation	PCL6 / PCL5e / IBM Proprinter / Epson PostScript Level 3 PDL / Barcode, Automatic Emulation Sensing
Print Monitor	SyncThru, SET IP
Fonts	1 Bit Map and 45 scaleable (35 Intellifont, 10 TrueType), 136 PS3 fonts
Consumables	High Yield: Replacement process unit < 8,000 pages. Normal Yield: Replacement process unit < 4,000 pages. Starter Process Unit Cartridge < 4,000 pages. Based on 5% coverage of A4 page (ISO mSO/IEC 19752 TBA)
STD Paper Handling	Manual feed, 50 sheet multi-purpose feeder(MPF) plus 250 sheet universal cassette
Opt'l Paper Handling	2nd universal cassette accepts 250 sheets
Duplexing	Automatic on 9330ND; Manual on 9330N (driver support provided)
Paper Drive	Envelope sizes: Monarch, No 9, No 10, C5, DL
Paper Type	MPF - paper, transparencies, labels, heavy paper stock, envelopes; Standard cassette - paper; Optional cassette - paper
Paper Weight	Cassette - 60-90gsm MPF - 60-163gsm Duplex 75-90gsm
Paper Size	MPF - A4, A5, A6, Letter, Legal, Folio, Executive, ISO B5, JIS B5, 3" x 5"; Standard Cassette - A4, A5, Letter Legal, Folio, Executive ISO B5, JIS, 3" x 5"; Optional Cassette - A4, A5, Letter, Legal, Folio, Executive ISO B5, JIS, 3" x 5"; Duplex - A4, Letter, Legal, Oficio, Folio
Paper Output	150 sheet face down, 1 sheet face up
Printable Area	Paper - 4mm from each side,10 mm from top and bottom
Physical Weight	< 10.6kg including consumable
PhysicalSize	400(w) x 433(d) x 285(h) mm
Power Voltage	220-240V 50/60Hz
Power Consumption	Less than 11 watts in sleep mode, Less than 900 watts printing (average)
Compliance	Energy Star Compliant
Workload	Up to 35,000 pages per month max, 4,000-7,000 per month avergae
Reliability MTBF	30,000 pages (Power on 8 hr/day in recommended duty cycle)
Reliability MTTR	30 minutes
Drivers	Windows 9.x/NT 4.0/2000/XP/ME/MAC/Vista, Posters, N-Up, Booklets, Duplex, Forms, Overlays, Watermarks
Temperature	10°C - 32°C (50°F - 89.6°F)
Humidity	10% - 80% relative humidity, non-condensing
Altitude	2,500 metres maximum
Acoustic	Printing - 54 dBA, Standby - 39 dBA, Sleepmode - Background Level
Warranty	2 years (Hot Swap)
Option 1	2nd cassette (250 sheet), 16/32/64/128Mb Memory
Note	Paper is a highly variable medium, and should be tested prior to purchase. Drum and Fuser Yields will vary based on job run length, media type, size, weight, orientation, and usage patterns.



© 2009 Printronix, Inc. All rights reserved. Genicom, Tally, TallyGenicom, TG TallyGenicom, the TG Logo, Intellifilter, Intelliprint and Intellipress are trademarks or registered trademarks of Printronix, Inc. Microsoft, Windows, and the Windows logo are trademarks or registered trademarks of Microsoft Corporation in the United States and/or other countries. All other trademarks, product names, company names or logos herein are the property of their respective owners. Product appearance and/or specifications are subject to change without notice.

Printed Date: 16/05/2009

PRINTRONIX®
GLOBAL PRINTING...ENABLED.

PRINTRONIX France Sarl
13 Rue Salomon de Rothschild
92150 Suresnes, France
Tel: +33 (0) 1 46 25 19 00
www.tallygenicom.com
emeasales@printronix.com