


ALL DIMENSIONS ARE
FOR REFERENCE ONLY

DIMENSIONS ARE IN INCHES [MILLIMETERS]
UNLESS OTHERWISE NOTED



PRODUCT SPECIFICATION SHEET				DWG NO	301-SP
REVISIONS				TITLE	
REV	ECO	DESCRIPTION			BY/DATE
A		INITIAL RELEASE			IB 5 JUN 96
				APPROVED	

SPECIFICATIONS

OVERALL HEIGHT 6 3/4 [171.5]

BASE MOUNTING HOLES .. 4 5/16 [109.5] BOLT CIRCLE

SHIPPING WEIGHT 2.7 POUNDS [1.2 KG]

COLOR SILVER PAINT

WISE OPENING 2 1/4 [57] MAXIMUM

MATERIAL;

1. 303 HEAD SEE 303-SP SHEET FOR SPECIFICATIONS

2. 300 BASE SEE 300-SP SHEET FOR SPECIFICATIONS

(OTHER JAWS AVAILABLE)

344 GROOVED BLACK NYLON

352 TEFLON

353 STEEL ZINC PLATED

354 BRASS

ALL DESIGN, OPERATIVE, AND PROCESS DATA PERTAINING TO THE ARTICLE ON THIS SHEET IS THE PROPERTY OF PANAVISE PRODUCTS, INC., RENO, NV. THIS INFORMATION IS DISCLOSED IN CONFIDENCE AND IS NOT TO BE COPIED, REPRODUCED, OR REVEALED TO OR APPROPRIATED BY OTHERS, IN PART OR IN WHOLE, WITHOUT THE EXPRESSED CONSENT OF PANAVISE. THIS PRINT IS LOANED, AND MUST NOT BE USED IN ANY MANNER DETRIMENTAL TO THE INTEREST OF PANAVISE, AND MUST BE RETURNED ON DEMAND



PANAVISE®

7540 Calbert Drive, Reno, Nevada 89511-1225
Phone (702) 850-2900, Fax (702) 850-2929

TITLE

STANDARD PANAVISE
MODEL 301

BASIC DIM. ENGLISH [ALTERNATE DIM. METRIC]

DRAWN	DATE	5	SCALE
I BENNETT	JUN 96	NONE	SHT 1 OF 1

SIZE
A

DWG. NO.

301-SP

REV

A