

GP Batteries

Data Sheet


Model No.: GP1604G

NO MERCURY ADDED

Description	: Mercury Free Layer Built Extra Heavy Duty Battery
Chemical System	: Carbon Zinc
Nominal Voltage	: 9.0 Volts
Nominal Dimensions	: 26.5 mm x 17.5 mm x 48.5 mm
Terminals	: Standard snap fastener stud (+) and socket(-)
Jacket	: Metal jacket
Applications	: All electronic devices, e.g. toys, remote controls
Warranty Period	: 24 months
Average Weight	: 37.5g

Estimated Service :

Discharge Resistance	Discharge Condition	End Point Voltage	Service Life
620 Ohms	2 Hrs/ Day 7 Days/ Week	5.40V	30.0 Hrs
180 Ohms	30 Mins/ Day 7 Days/ Week	4.80V	8.6 Hrs



Cross References:

GP	JIS	IEC	Eveready
1604G	6F22	6F22	1222

