


ISORYL SCREWDRIVERS

ISORYL SCREWDRIVER SETS

▼ ISORYL SCREWDRIVER SETS

▷ NF ISO 2380 -1, -2 ; DIN 5261, 5262, 5264,
5265 ; NF ISO 8764 -1, -2 ; DIN 5260 -1, -2



Icon	Icon	Icon				Number of screwdrivers	ΔΔ g
AR.J5	AR.J55		● AR.3 x 75 6,5 x 150	4 x 100 AG.8 x 200	5,5 x 100	5	406 541
	AS.2		● AB.4 x 100 10 x 200	6,5 x 150	8 x 200	4	504
	AS.4		⊕ AP.0 x 50 3 x 150	1 x 75 4 x 200	2 x 100	5	685
		AT.J9	● AR.3 x 75 ⊕ AP.0 x 50 ○ 84.2 - 2,5 - 3	3,5 x 100 1 x 75	4 x 100 2 x 100	9	300
AJ.3	AS.15		● AR.3,5 x 75 6,5 x 150	4 x 100	5,5 x 100	14	1210 1460
			● AG.8 x 150 ⊕ AP.1 x 75 ⊕ AD.1 x 75 ● AF (screw starters)	8E x 200 2 x 100 2 x 100	AY.3,5 x 100 VE 3 x 150 3 x 150		

ISORYL SCREWDRIVERS FOR SLOTTED HEADS

▼ AR FOR SLOTTED HEADS - MACHINED BLADES

- Shank machined for access into recesses.
- Polished chrome finish.

Icon	e x A mm	T mm	Ø1 x L1 mm	Ø2 x L2 mm	L mm	ΔΔ g
AR.2X40	0,4 x 2,0	0,2	2,0 x 40	16,0 x 70	110	13,5
AR.2,5X50	0,4 x 2,5	0,2	2,5 x 50	16,0 x 70	120	15
AR.2,5X75	0,4 x 2,5	0,2	2,5 x 75	16,0 x 70	145	16
AR.3X75	0,5 x 3,0	0,3	3,0 x 75	16,0 x 70	145	17,5
AR.3,5X75	0,6 x 3,5	0,4	3,5 x 75	20,5 x 80	155	31
AR.3,5X100	0,8 x 4,0	0,4	3,5 x 100	20,5 x 80	180	33
AR.4X100	0,8 x 4,0	0,5	4,0 x 100	24,0 x 90	190	45
AR.4X150	0,8 x 4,0	0,5	4,0 x 150	24,0 x 90	240	50
AR.5,5X100	1,0 x 5,5	0,6	5,5 x 100	28,0 x 100	200	71
AR.5,5X150	1,0 x 5,5	0,6	5,5 x 150	28,0 x 100	250	80
AR.6,5X100	1,2 x 6,5	0,7	6,5 x 100	30,0 x 110	210	102
AR.6,5X150	1,2 x 6,5	0,7	6,5 x 150	30,0 x 110	260	114
AR.8X150	1,2 x 8,0	0,7	8,0 x 150	30,0 x 110	260	141

