



© COPYRIGHT 1975-83 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					DATE	APPROVED
P	F	ZONE	LTR	DESCRIPTION		
✓	✓		E	REV PER AD-5084	2-1-91	RF
✓	✓		F	REV PER 0310-0146-96	2-27-96	SAS
			F1	REVISED PER ECO-09-025273	16NOV08	AEG



① WILL ALSO MATE W/OTHER CONNECTORS WHICH ARE COMPATIBLE WITH THE .066 & .150 END DIMS.

② OBSOLETE PART NUMBER

③ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

③ OBSOLETE	3.132	3.032	2.806	.106	2.890	.190	3.804	3.604	3.200	2.900	29	60	2-87496-6
	3.032	2.932	2.706		2.790		3.704	3.504	3.100	2.800	28	58	2-87496-5
	2.932	2.832	2.606		2.690		3.604	3.404	3.000	2.700	27	56	2-87496-4
	2.832	2.732	2.506		2.590		3.504	3.304	2.900	2.600	26	54	2-87496-3
	2.732	2.632	2.406		2.490		3.404	3.204	2.800	2.500	25	52	2-87496-2
	2.632	2.532	2.206		2.290		3.304	3.104	2.700	2.400	24	50	2-87496-1
	2.532	2.432	2.106		2.190		3.204	3.004	2.600	2.300	23	48	2-87496-0
	2.432	2.332	2.006		2.090		3.104	2.904	2.500	2.200	22	46	2-87496-0
	2.332	2.232	1.906		1.990		3.004	2.804	2.400	2.100	21	44	1-87496-9
	2.232	2.132	1.806		1.890		2.904	2.704	2.300	2.000	20	42	1-87496-8
③ OBSOLETE	2.132	2.032	1.706		1.790		2.804	2.604	2.200	1.900	19	40	1-87496-7
	2.032	1.932	1.606		1.690		2.704	2.504	2.100	1.800	18	38	1-87496-6
	1.932	1.832	1.506		1.590		2.604	2.404	2.000	1.700	17	36	1-87496-5
③ OBSOLETE	1.832	1.732	1.406		1.490		2.504	2.304	1.900	1.600	16	34	1-87496-4
	1.732	1.632	1.306		1.390		2.404	2.204	1.800	1.500	15	32	1-87496-3
③ OBSOLETE	1.632	1.532	1.206		1.290		2.304	2.104	1.700	1.400	14	30	1-87496-2
	1.532	1.432	1.106		1.190		2.204	2.004	1.600	1.300	13	28	1-87496-1
③ OBSOLETE	1.432	1.332	1.006		1.090		2.104	1.904	1.500	1.200	12	26	1-87496-0
	1.332	1.232	.906		.990		2.004	1.804	1.400	1.100	11	24	1-87496-0
	1.232	1.132	.806		.890		1.904	1.704	1.300	1.000	10	22	1-87496-0
	1.132	1.032	.706		.790		1.804	1.604	1.200	.900	9	20	1-87496-0
	1.032	.932	.606		.690		1.704	1.504	1.100	.800	8	18	1-87496-0
	.932	.832	.506		.590		1.604	1.404	1.000	.700	7	16	1-87496-0
	.832	.732	.406		.490		1.504	1.304	.900	.600	6	14	1-87496-0
	.732	.632	.306		.390		1.404	1.204	.800	.500	5	12	1-87496-0
	.632	.532	.206		.290		1.304	1.104	.700	.400	4	10	1-87496-0
	2.632	2.532	2.306	.106	2.390	.190	3.304	3.104	2.700	2.400	24	50	87496-1
	L	K	J	H	G	F	E	D	C	B	A	NO. OF POS.	PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES.
TOLERANCES ON:
DECIMALS ±.005
ANGLES ±

MATERIAL
WSG. - GLASS FILLED NYLON
COLOR: BLACK
POST - PHOS. BRONZE
FINISH
POST - .00030 GOLD OVER
.00050 NICKEL

CONTRACT NO

DR *D. J. J. 8/21/75*

CHK *D. J. J. 8-22-75*

APPD *B. Bennett 8/25/75*

APPD *R. Clark 8/25/75*

DSGN APPD

OTHER APPD

AMP INCORPORATED
Harrisburg, Pa.

NAME

HEADER ASSY. MOD II 100x100
CENTERS WITH PIN. PROTECTION
BOTH SIDES & MTG. EARS
(MATES W/AMP LATCH OR FCC ONE SIDE) ①
& MOD IV OTHER SIDE

SIZE CODE IDENT NO DRAWING NO

C

00779

87496

SCALE

SHEET

10-1