

## Panel Meters



### OEM Series



**— NEW —**

OEM Series — Aimed at high volume use. A range of digital panel meters particularly suited for high volume use. All modules feature a 3½ digit LCD display and 7-9 VDC

operation. Available in packs of 10, supplied with mounting bezel.

Stock No.	Mfr.'s Type	Module Function	Digit Ht. (in.)	Approx. Size (in.)	Supply Voltage	Measurement Ranges	PER PKG./10
572-0019	V1	LCD Voltmeter	0.25	1.50 × 0.55	9 VDC	+ 200 mVDC	119.90
572-0020	V125	LCD Voltmeter	0.50	1.81 × 0.80	9 VDC	+ 200 mVDC	129.90
572-0021	V600	LCD Voltmeter	0.63	2.68 × 1.18	9 VDC	+ 200 mVDC	139.90
572-0022	OEM EV	OEM Series evaluation pack. Contains one of each of the above.					49.95

### SP Series — Splashproof Ultra Low Profile

**— NEW —**



Splashproof, ultra low profile, 3½ digit snap-in meters with gasket. The SP Series can be front or rear panel mounted. 12 pin versions allow more modes of operation and compatibility with competing types. 8 pin versions are lower cost, easier to use and more suited to new designs

Stock No.	Mfr.'s Type	Module Function	Digit Ht. (in.)	Module Size (in.)	Panel Cut-Out (in.)	No. of Pins	Supply Voltage	Measurement Ranges	EACH
572-0023	SP 100	LED voltmeter	0.36	1.38 × 0.88	1.34 × 0.84	12	5 VDC	±200 mVDC	39.90
572-0024	SP 200	LCD voltmeter, backlit, single rail	0.36	1.38 × 0.88	1.34 × 0.84	12	3-7 VDC	±200 mVDC	30.95
572-0025	SP 300	LED voltmeter	0.36	1.38 × 0.88	1.34 × 0.84	8	5 VDC	±200 mVDC	33.95
572-0026	SP 400	LCD voltmeter, backlit, single rail	0.36	1.38 × 0.88	1.34 × 0.84	8	3-7 VDC	±200 mVDC	26.95

### EM Series — Round Hole Mounting Digital Panel Meters



Now anyone with a drill can mount a digital panel meter in less than a minute. Modules in EM Series are fitted with a threaded stud allowing users to mount the product through a 7/32" hole.

Stock No.	Mfr.'s Type	Module Function	Digit Ht. (in.)	Module Size (in.)	Mounting Hole (in.)	Connection (Wires)	Supply Voltage	Measurement Ranges	EACH
572-0001	EMV 1125	3½ digit, low cost, LCD voltmeter	0.50	1.71 × 0.84	7/32	10	7.5-15 VDC	±200 mVDC	24.95
572-0002	EMV 1200	3 digit, signal powered, LCD voltmeter	0.50	1.71 × 0.84	7/32	2	3.0-50 VDC	24.95	
572-0003	EMT 1900	3½ digit LCD thermometer	0.50	1.71 × 0.84	7/32	min. 2	4.0-28 VDC	24.95	
572-0004	EMC 1500	5 digit LCD hour meter	0.35	1.71 × 0.84	7/32	min. 3	5.0-27 VDC	-14 to +122°F -4 to +428°F 9999.9 hrs. 99999 hrs.	24.95
572-0005	EMA 1710	LCD analog style panel meter	—	1.71 × 0.84	7/32	3	5.0-12 VDC	0-1 VDC	19.95

### 10 Series — Snap-In Sub-Miniature Digital Panel Meters



A range of snap-in, sub-miniature digital panel instruments with LED backlighting for low light conditions and single rail operation for ease of use. LED and 4-20 mA versions of the

range are also available.

Stock No.	Mfr.'s Type	Module Function	Digit Ht. (in.)	Module Size (in.)	Panel Cut-Out	Snap-In Bezel	Single Rail	LED Backlit	Screw Term.	Supply Voltage	Measurement Ranges	EACH
572-0006	DPM 1S-BL	3½ digit LCD voltmeter, backlit, single rail	0.22	1.18 × 0.55	1.12 × 0.45	✓	✓	✓	—	3-7 VDC	±200 mVDC	34.95
572-0007	DPM 2S-BL	3½ digit LCD voltmeter, backlit, single rail	0.32	1.38 × 0.67	1.30 × 0.60	✓	✓	✓	—	3-7 VDC	±200 mVDC	37.95
572-0009	DPM 3S-BL	3½ digit LCD voltmeter, backlit, single rail	0.43	1.57 × 0.79	1.50 × 0.71	✓	✓	✓	—	3-7 VDC	±200 mVDC	35.95
572-0010	DPM 342	3½ digit LCD 4-20 mA meter, backlit	0.43	1.57 × 0.79	1.50 × 0.71	✓	—	✓	✓	Loop-Powered	4-20 mA	67.36
572-0011	DPM 340	3½ digit LED voltmeter	0.30	1.57 × 0.79	1.50 × 0.71	✓	✓	—	—	5 VDC	±200 mVDC	39.95

**Prices Subject To Change — We Always Ship At The Lowest Price In Effect**

**ALLIED ► 1019**

16