






PRODUCT NO.	PLATING VARIATIONS		PLASTIC COLOR
SEE TABLE			
DASH NO.	OVERPLATING	UNDERPLATING	
XXXXX-1YY	30u"/.76u Au	50u"/1.27u Ni	
-2YY	15u"/.38u Au	50u"/1.27u Ni	CREAM
-3YY	50u"/1.27u Au	50u"/1.27u Ni	NATURAL BROWN
-4YY	150u"/3.81u 93/7 TIN LEAD		BLACK
-5YY	15u"/.38u Pd ALLOY WITH Au FLASH	50u"/1.27u Ni	DARK BLUE
XXXXX-6YY	30u"/.76u Pd ALLOY WITH Au FLASH	50u"/1.27u Ni	LIGHT BLUE

PART NUMBER INFORMATION

XXXXX-YYY

PRODUCT
BASE NO


NO OF POSITIONS
SEE NOTE 5

PIN PART NO &
PLASTIC COLOR

EXAMPLE: 65566-408 DENOTES AN 8 POSITION PART WITH
.00381/.000150 TIN PLATED PINS.
THE OVERALL PLASTIC LENGTH
IS 1.174/29.82.
THE PLASTIC COLOR IS BLACK.



NOTES:

- ① PLASTIC MATERIAL: 20% MIN GLASS FILLED NYLON. RATED PER UL 94V-0.
PIN MATERIAL: 3/4 HARD PHOS. BRONZE.
- ② MEASURED AT DATUM -D- WITH PART IN RESTRAINED CONDITION.
- ③ 5 LBS. / 2.3 KG MINIMUM PIN PUSH-OUT FORCE IN EITHER DIRECTION.
- ④ SEE TABLE FOR AVAILABLE DASH NO'S (AVAILABILITY DENOTED BY ASTERISK).
- ⑤ MIN NO. OF POSITIONS - 1 , MAX NO. OF POSITIONS - 31.
- ⑥ DIM L - (NUMBER OF POSITIONS X .150/3.81) - .026/0.66.
- ⑦ .020/.51 MAX FLASH AROUND PINS IN THIS AREA.
- ⑧ .030/.76 MAX FLASH AROUND PINS IN THIS AREA.
- ⑨ TWO SIDES OF LEAD-IN ON PINS NOT PLATED. TYPICAL BOTH ENDS.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		 ELECTRONICS www.fciconnect.com	
ltr	ecn no	dr	date	linear	.XX±.01/X ±.3	projection 	title BERGSTIK® I HEADER .150/3.81cc SR STRAIGHT	product family BERGSTIK	code 22526
U					.XXX±.005/.XX ±.13 .XXXX±.0020/.XXX ±.051				
					angles 0° ±2°				
				dr	J. W. BAIR 4/26/89	INCH/MM 	size dwg no 65560	sheet 2 of 4	
				engr	M. LEACH 4/26/89				
				chr	M. LEACH 4/26/89				
				appd	M. LEACH 4/26/89	scale 1 : 1			
sheet index	revision sheet								



PRODUCT NO. SEE TABLE	TOTAL PIN LENGTH DIM A	TAIL LENGTH DIM B	MATING LENGTH DIM C	DASH NUMBERS AVAILABLE					
				-1XX	-2XX	-3XX	-4XX	-5XX	-6XX
65560-YYY	.825/20.99	.495/12.57	.230/5.84	*	*	*	*		
65561-YYY	.615/15.62	.285/7.24	.230/5.84	*	*	*	*		
65562-YYY	.730/18.54	.400/10.16	.230/5.84	*	*	*	*		*
65563-YYY	.965/24.51	.635/16.13	.230/5.84	*	*	*	*		
65564-YYY	1.025/26.04	.695/17.65	.230/5.84	*	*	*	*		
65565-YYY	.525/13.34	.195/4.95	.230/5.84	*	*	*	*		
65566-YYY	.450/11.43	.120/3.05	.230/5.84	*	*	*	*		*
65567-YYY	.480/12.19	.150/3.81	.230/5.84	*	*	*	*		
65568-YYY	.425/10.80	.095/2.41	.230/5.84	*	*	*	*		
65569-YYY	.580/14.73	.250/6.35	.230/5.84	*	*	*	*		
65570-YYY	NOT AVAILABLE								
65571-YYY	1.095/27.81	.765/19.43	.230/5.84	*	*	*	*		
65572-YYY	.925/23.50	.595/15.11	.230/5.84	*	*	*	*		
65573-YYY	1.155/29.34	.825/20.96	.230/5.84	*	*	*	*		
65574-YYY	.880/22.35	.550/13.97	.230/5.84	*	*	*	*		
65575-YYY	.615/15.65	.185/4.70	.330/8.38	*	*	*	*		
65576-YYY	.555/14.10	.125/3.18	.330/8.38	*	*	*	*		
65607-YYY	.895/22.73	.245/6.22	.550/13.97	*	*	*	*		
65608-YYY	1.195/30.35	.545/13.84	.550/13.97	*	*	*	*		
66472-YYY	NOT AVAILABLE								
66561-YYY	.815/20.70	.120/3.05	.595/15.11	*	*	*	*		
67097-YYY	.436/11.07	.216/5.49	.120/3.05	*	*	*	*		
67159-YYY	.634/16.10	.216/5.49	.318/8.08	*	*	*	*		
67161-YYY	NOT AVAILABLE								
67282-YYY	NOT AVAILABLE								

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		 ELECTRONICS www.fciconnect.com		
ltr	ecn no	dr	date	linear	.XX±.01/X ±.3		projection 	title BERGSTIK® I HEADER .150/3.81cc SR STRAIGHT			
U					.XXX±.005/XX ±.13						
					.XXXX±.0020/XXX ±.051						
				angles	0° ±2°			product family BERGSTIK size dwg no 65560			
		dr	J. W. BAIR	4/26/89							
		engr	M. LEACH	4/26/89							
		chr	M. LEACH	4/26/89	scale 1 : 1		A 65560				
		appd	M. LEACH	4/26/89							
sheet index	revision sheet										



PRODUCT NO.	TOTAL PIN LENGTH DIM A	TAIL LENGTH DIM B	MATING LENGTH DIM C	DASH NUMBERS AVAILABLE					
SEE TABLE				-1XX	-2XX	-3XX	-4XX	-5XX	-6XX
67468-YYY	NOT AVAILABLE								
68793-YYY	1.028/26.11	.318/8.08	.610/15.49	*					
86882-YYY	.630/16.00	.110/2.79	.420/10.67			*			
86883-YYY	1.335/33.91	.585/14.86	.650/16.51			*			

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		 ELECTRONICS www.fciconnect.com	
ltr	ecr no	dr	date	linear	.XX±.01/X ±.3		projection 	title BERGSTIK® I HEADER .150/3.81cc SR STRAIGHT		
U					.XXX±.005/.XX ±.13					
					.XXXX±.0020/.XXX ±.051					
				angles	0° ±2°			product family BERGSTIK size dwg no A 65560		
				dr	J. W. BAIR	4/26/89				
				engr	M. LEACH	4/26/89				
				chr	M. LEACH	4/26/89	scale 1 : 1		sheet 4 of 4	
				appd	M. LEACH	4/26/89				
sheet index		revision sheet								