

## FACOM® INSULATED VSE DIAGONAL CUTTERS



- › 2 color warning handle insulation - color changes from orange to yellow if insulation integrity compromised.
- › Inset joint.
- › Burnished nose.



Product #	Size (in)	Overall Length (in) (L)	Jaw Length (in) (A)	Jaw Width (in) (B)	Weight (lbs)
FA-391.16AVSE	6-1/2	6-5/16	3/4	13/32	0.47

## WIRE STRIPPER - CRIMPER

- › Strips 10-22 AWG (American Wire Gauge).
- › Box style crimp.
- › Crimps insulated and non-insulated terminals for 10-22 AWG.
- › Crimps non-insulated 7 mm and 8 mm auto ignition wire.
- › Cuts screw/bolt sizes 4-40, 5-40, 6-32, 8-32, 10-32, 10-24.
- › Anvil type wire cutter for cutting copper wire.
- › Air-pocket cushion grips for comfort.



Product #	Overall Length (in) (L)	Weight (lbs)
J299	8-1/2	0.45



## WIRE STRIPPER - CUTTER

- › Strips wire sizes 10, 12, 14, 16, 18, and 20 AWG (American Wire Gauge).
- › Wire cutter for copper wire.
- › Plier nose for pulling and looping wire.
- › Spring return and convenient handle lock.
- › Platisol grips for added comfort.




Product #	Overall Length (in) (L)	Weight (lbs)
J297	6-1/16	0.21



## WIRE STRIPPER

- › Strips wire sizes 22, 24, 26, 28, and 30 AWG (American Wire Gauge).
- › Wire cutter.
- › Plier nose for pulling and looping wire.
- › Automatic spring return.
- › Platisol grips for added comfort.



Product #	Overall Length (in) (L)	Weight (lbs)
J296	6-1/16	0.21

