

PRODUCT INFORMATION

Item	Content
Class Code	XJA042
Series	NU
Product number	RNU1C271MDN1
Category Temperature Range	-55 to +105 cel
Rated voltage	16 V
Rated capacitance	270 μ F
Tolerance rated capacitance	-20 to +20%
Tangent of loss angle	0.08
Leakage current (short term)	864 μ A
Diameter : D	8 mm
Length : L	13 mm
Rated Ripple Current (at 100kHz)	5000 m A
ESR	8 m Ohm
Mass	0.93 g
Packing Type	Bulk(Long Lead)
Quantity in the standard packing	2000
Surface mounting flag	FALSE
Environmental Matter	Lead(Pb) free and RoHS compliant.
Product Lifecycle Stage	PROD
Type	Lead Type
Package Type	04 type(JIS C 5101-1)
	Conductive Polymer Aluminum Solid Electrolytic

[JAPANESE](#)

Copyright (C) 2007 NICHICON CORPORATION