

NAVIGATE THE CATALOG BY SECTION

[1](#)
[2](#)
[3](#)
[4](#)
[5](#)
[6](#)
[7](#)
[8](#)
[9](#)
[10](#)
[11](#)
[12](#)
[13](#)
[14](#)
[15](#)
[16](#)
[17](#)
[18](#)
[19](#)




LAPP ONLINE CATALOG

EPIC® Pin & Sleeve Connectors

20 Amp: North American Version

ALUPRES Aluminum Enclosures Direct Connect



TECHNICAL DATA

Impact Resistance:

8J

Ambient Temperature:

-25°C to 70°C

Flame Resistance:

➤ **Glow Wire Test: Enclosure:**

850°C

➤ **Glow Wire Test: Contact Enclosure:**

850°C

➤ **Self-Extinguishing: Enclosure:**

UL94-V2

➤ **Self-Extinguishing: Contact Carrier:**

UL94-V2

PART NUMBERS

Part Number	Voltage	# of Wires	# of Poles	Ground-Clock Position
720124FX	125	3	1+N+PE	4
720126FX	250	3	2+PE	6
720127FX	480	3	2+PE	7
720123FX	250 DC	3	2+PE	3
721132FX	125 / 250	4	2+N+PE	12
720139FX	3Ø250	4	3+PE	9
720137FX	3Ø480	4	3+PE	7
720135FX	3Ø600	4	3+PE	5
720149FX	3ØY 120 / 208	5	3+N+PE	9
720147FX	3ØY 277 / 480	5	3+N+PE	7
720145FX	3ØY 347 / 600	5	3+N+PE	5
720142FX	50-250 (500 Hz)	5	3+N+PE	2

MATING COMPONENTS

- [MULTIMAX Male Plug with Cable Sleeve, IP 44](#)
- [CEE Straight Male Plug with Cable Gland, IP 44](#)
- [CEE 90° Male Plug with Cable Gland, IP 44](#)
- [CEE Angled 82° Male Inlet, IP 44](#)



DOWNLOAD PDF CATALOG PAGE

LAPP USA • LAPP CANADA • LAPP MEXICO

Headquarters: 29 Hanover Road, Florham Park, NJ 07932
800-774-3539 • FAX: 973-660-9330 • sales@lappusa.com