


CABLE SIZE	CABLE TYPE	GAUGE (AWG)
0.250(6,4)	SV SVT	18/2 18/2
0.255(6,5)	SV SVT	18/3 18/3
0.290(7,4)	HPD	16/2

NOTES:

1. UL recognized and CSA approved
2. Color: Black
3. Material: Nylon type 6 heat stabilized
4. Flammability Rating: UL94V-2
5. Temperature Rating: Up to 105 °C



REVISIONS			DOC. NO. SPC-F005 * Effective: 12/21/98 * DCP No: 680						
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
182	B	REDRAWN & UPDATED	HYO	11/8/99	JC	12/11/00	JC	12/11/00	
1779	C	ROHS ADDED	DCM	1/24/06	JWM	1/24/06	JWM	1/24/06	

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

Tolerances Unless Otherwise Specified Decimal .XXX ± 0.005	DRAWN BY:	DATE:	DRAWING TITLE:			
	J.C	2/18/91	Strain Relief Bushing			
	CHECKED BY:	DATE:	SIZE	DWG. NO.	ELECTRONIC FILE	REV
	APPROVED BY:	DATE:	A	SRR-10	46N7808.dwg	C
SCALE: NTS			U.O.M.: INCHES [mm]		SHEET: 1 OF 1	