

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [82-26-3809](#)
Status: **Active**
Description: 1.50mm Pitch Round Conductor Flat Cable - 26 AWG (7 x 34) Stranded, Topcoat, 9 Circuits, Reel 30.48m Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	LR61126
UL	E61522

General

Product Family	Cable
Series	24483
Crimp Quality Equipment	Yes
Geographic Area	Asia
Product Name	Ribbon
UPC	800754986540

Physical

Cable Length	30.48m
Circuits (Loaded)	9
Insulation	PVC
Packaging Type	Reel
Pitch - Termination Interface	1.50mm
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	26
Wire/Cable Type	(7x34) Stranded, Topcoat

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	300V

Material Info

Old Part Number	24483-09-100B
-----------------	---------------

Reference - Drawing Numbers

Sales Drawing	SD-24483-001
---------------	--------------



image - Reference only **Series**

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[24483Series](#)

Use With
[52004](#) Wire Trap. [51016](#) Cable Holder